



Sample photo

Order symbol: ALN 060605
Product nbr: 7811060
Description: Enclosure
Remarks: Aluminium

EAN: 6418074016034
El. number:
Finland:
:

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		66	60	46	Ingress Protection (EN 60529): IP 66/67/68
inch:		2.6	2.4	1.8	Impact Resistance (EN 62262): IK 08
Materials:					NEMA Class: NEMA 1, 4, 4X, 12, 13
Material:	Aluminium				Certificates: Underwriters Laboratories Fimko UL Canada Gost R
Base colour:	RAL 7001				
Cover colour:	RAL 7001				
Cover screws material:	Stainless steel				
Gasket material:	Polyurethane				
Temperatures:					
Short term:	-50 ... 140 °C				
Continuous:	-50 ... 80 °C				
Short term:	-60 ... 285 °F				
Continuous:	-60 ... 175 °F				
Accessories:					
TRM 0507	DIN-15 Mounting rail				
MIV 5	DIN-35 Mounting rail				
MR 75003	Selftapping taptite screw M3				
MRS 28540	Wall fastening lug (2 pcs)				

