



ENGLISH

Datasheet

Stock No: 361-800

**RS Pro Brown, 2491X Equipment Wire, 1.5 mm<sup>2</sup>  
CSA , 450/750 V ac 15 A 15 AWG, 100m**



## Product Details

### 2491X

A plain copper stranded conductor covered by a PVC insulated sheath. These flexible wires are intended for use in internal wiring applications in electrical and electronic equipment, or runs within covered ducts, conduits.

#### Features & Benefits:

- \* Flexible class 5 conductors
- \* BS6004 Conductors
- \* Plain annealed copper conductors

#### Note

The RS Brand range of products has been certified by engineers as offering comparable quality to that of leading brands without the premium price tag

## Specifications

Cross Sectional Area	1.5 mm <sup>2</sup>
Sheath Colour	Brown
Core Strands	30/0.25 mm
Insulation Material	PVC
Outer Diameter	3.4mm
Length	100m
Number of Strands	30
Current Rating	15 A
Voltage Rating	450/750 V ac
Size of Strands	0.25 mm
American Wire Gauge	15 AWG
Conductor Material	Annealed Copper
Cable Shape	Single Core
Type	2491X
Shield Type	Unshielded
Standards Met	BASEC
European Harmonised Code	H07V-K
Insulation Wall Thickness	0.7mm