

UNILITE HELMET MOUNTABLE LED HEADLIGHT

PS-H4



7½-60
HOURS
RUNTIME

85
METRE
BEAM RANGE

200
LUMENS
OUTPUT

IPX4
WATER
RESISTANCE

- » 200 Lumen white CREE LED
- » 6 lighting modes
- » 2Hz safety flashing mode
- » Sliding diffuser for focused or flood lighting features
- » 5mm red LED for night vision
- » 90° rotational head
- » Industrially tough polymer housing
- » Fully adjustable non-slip silicone headband
- » 3M VHB adhesive helmet mount (Included)
- » Bike helmet velcro strap (Included)
- » IPX4 water resistant

BATTERY 3 x 1.5v AAA Duracell Alkaline Batteries (included)
WEIGHT 100g (with batteries)
DIMENSION Headlight: 38 x 70 x 50mm

EMERGENCY FLASH



LIGHT BY
CREE
LEDs



3M ADHESIVE HELMET MOUNT (INC.)



RED LED FOR NIGHT VISION



NON-SLIP SILICONE HEAD STRAP



BIKE HELMET VELCRO STRAP (INC.)