

Datasheet

RS Pro 2kW Fan Heater, Portable, Type C - European Plug

RS Stock No: **839-5274**



Product Details

RS Pro fan heater delivers a maximum power of 2 kW with airflow of up to 100 m³/h. This portable unit is fitted with PTC ceramic heating elements, which heat the air quickly and efficiently, making it perfect for use in living rooms and offices. It features multistage temperature control with three heating stages. The fan offers connection through type C European plug.

Features and Benefits

- Multistage temperature control with 3 heating stages
- Integrated room thermostat for consistent heat levels
- Overheat protection
- Fan motor with thermal protection
- Fully portable
- Heating performance stage 1: 1 kW
- Heating performance stage 2: 2 kW
- Air flow rate: 100 m/h
- Power consumption: 8.69 A
- Supply voltage of 230 V/50 Hz



ENGLISH

Specifications:

| | |
|----------------------|---------------------------|
| Air Flow | 100 m ³ /h |
| Control Type | On/Off Switch, Thermostat |
| Depth | 130 mm |
| Dimensions | 225 x 165 x 130 mm |
| Frequency | 50 Hz |
| Heat Type | Fan |
| Height | 225 mm |
| Maximum Output Power | 2 kW |
| Mounting | Portable |
| Noise Level | 45 dB(A) |
| Plug Type | Type C - Euro Plug |
| Power Settings | 3 |
| Width | 165 mm |
| Voltage Rating | 240 V |