





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	ECN	DATE	APVD
J	-						
			O	RELEASED	FJ00-0784-02	15APR02	ES
			A	REVISED	FJA0-0420-04	05JUL04	A.O
			B	REVISED	ECR-10-007856	13APR10	TS



1. APPLICABLE TERMINAL P/N: 353376 (WIRE RANGE: AVSS, CAVS 0.3~0.5mm²)
APPLICABLE FERRITE P/N: 353379
2. THIS PRODUCT SHOULD BE USED WITH THE IIDIA SQUIB CONNECTOR SLIM TYPE LOCKING BUTTON (P/N: 1612119).
3. MATING SHORT-CIRCUIT RING PART NUMBER: 699638, 1376766, 1473369
4. ABOUT THE FORM OF INTERFACE, SEE THE DRAWING OF SHORT-CIRCUIT RING.
5. INSTRUCTION SHEET: 411-78040.
1. 適用端子P/N: 353376 (AVSS, CAVS 0.3~0.5mm²)
適用フェライトP/N: 353379
2. 本製品は、IIDIA SQUIB CONNECTOR SLIM TYPE LOCKING BUTTON (P/N: 1612119) を装着して使用する。
3. 本製品が適応するショートサーキットリング品番は、699638, 1376766, 1473369
4. 嵌合相手形状は、ショートサーキットリング図面を参照のこと。
5. 取扱説明書: 411-78040



RIB POSITION

C	ORANGE	1612120-3
B	YELLOW	1612120-2
A	YELLOW	1612120-1
RIB POSITION	COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN E. SASAKI 15APR02	Tyco Electronics Corporation Kawasaki, Japan			
DIMENSIONS: 単位: ㎜		CHK T. KOHNO 15APR02				
TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.2		APVD N. SAI 15APR02	NAME IIDIA SQUIB CONNECTOR SLIM TYPE MK-II PLUG HOUSING			
0-PLC ± 1-PLC ±0.1 2-PLC ±0.01 3-PLC ±0.001 4-PLC ±0.0001 ANGLES ±1.00°		PRODUCT SPEC 108-5818				
MATERIAL PBT		APPLICATION SPEC 114-5234	SIZE A3			
FINISH SEE TABLE		WEIGHT 1.6 g				
CUSTOMER DRAWING			CAGE CODE 00779	DRAWING NO 1612120	RESTRICTED TO -	
			SCALE 3:1	SHEET 1	OF 1	REV B