

Fiber optic contact insert - VC-FSMA-M-2 SET - 1855432

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)




Quick mounting plug for polymer fiber cable, for the contact carrier module VC-AFOS 2, length: 27 mm, width: 7 mm, 2 pcs. each as set

Why buy this product

- Clear representation
- For a variety of applications



Key commercial data

Packing unit	1 pc
GTIN	 4 017918 162696
Weight per Piece (excluding packing)	16.5 g
Custom tariff number	85367000
Country of origin	Poland

Technical data

Mechanical characteristics

Number of positions	1
Connection profile	F-SMA type 905, IEC 874-2
Fiber type	Polymer Fiber
Fiber	Polymer fiber, 980/1000 µm
Insertion/withdrawal cycles	> 100
Tightening torque, min.	0.1 Nm
Tightening torque max.	0.2 Nm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 70 °C
Degree of protection	IP20

Material data

Housing material	Nickel silver
------------------	---------------

Fiber optic contact insert - VC-FSMA-M-2 SET - 1855432

Technical data

Material data

Contact material	Nickel silver
------------------	---------------

Optical characteristics

Attenuation	< 3 dB
-------------	--------

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440209

ETIM

ETIM 2.0	EC000438
ETIM 3.0	EC000438
ETIM 4.0	EC000438
ETIM 5.0	EC000438

UNSPSC

UNSPSC 6.01	30211923
UNSPSC 7.0901	39121522
UNSPSC 11	39121522
UNSPSC 12.01	39121522
UNSPSC 13.2	39121522

Approvals

Approvals

Approvals

GOST / GOST

Ex Approvals

Approvals submitted

Fiber optic contact insert - VC-FSMA-M-2 SET - 1855432

Approvals

Approval details

GOST 

GOST 

Accessories

Accessories

Assembly tool

Assembly tool - PSM-SET-FSMA-POLISH - 2799348



Polymer fiber polishing set, for F-SMA quick mounting connectors

Stripping tool - PSM-FO-STRIP - 2744199



Stripping pliers for transmitting individual elements of the fiber optic cable. Especially suited for all polymer and HCS cables. Special mechanics and precise blade form avoid damage to the fiber optic fibers. Dimensions: (L x W x H) 160 x 130 x 36 mm.

Polisher - VC-POLISHER/M FSMA - 1884982



Polisher, metal, for repeated preparation of VARIOCON fiber optic ferrules

Drawings

Fiber optic contact insert - VC-FSMA-M-2 SET - 1855432

Dimensioned drawing

