




PRODUCT NUMBER
90311-004
90311-004LF
SEE NOTE 2



mat'l. code SEE NOTE 1				surface ✓		tolerance tolerances unless otherwise specified		projection MM/INCH		product family MINITEK HOUSINGS		
ltr	ecr no	dr	date	angles		linear		MM/INCH		title		
T						X*3/XX*.01				MINITEK CTW HSG. DBL ROW		
						XX*.13/XXX*.005		scale 5:1		POLARIZATION & LATCHING		
						XXX*.051/XXXX*.0020				dwg no		
				dr		D. WHITING 1991-02-15		FCJ		sheet 2 of 3		
				engr		S. OLSON 1991-02-15				size		
				chr		S. OLSON 1991-02-15				A3		
				appd		S. OLSON 1991-02-15				type		
sheet		revision								Product Customer Drawing		
index		sheet										

PRODUCT NUMBER	POS.	DIM A	DIM B	DIM C	LATCHING FEATURES	EQUIVALENT HIGH-TEMP P/N
90311-004LF	2 x 2	2.0/.08	4.4/.17	2.2/.09	1 (SHEET 2)	10087010-004LF
90311-006LF	2 x 3	4.0/.16	6.4/.25	3.2/.13	2 (SHEET 1)	10087010-006LF
90311-008LF	2 x 4	6.0/.24	8.4/.33	4.2/.17	2 (SHEET 1)	10087010-008LF
90311-010LF	2 x 5	8.0/.32	10.4/.41	5.2/.21	2 (SHEET 1)	10087010-010LF
90311-012LF	2 x 6	10.0/.39	12.4/.49	6.2/.24	2 (SHEET 1)	10087010-012LF
90311-014LF	2 x 7	12.0/.47	14.4/.57	7.2/.28	2 (SHEET 1)	10087010-014LF
90311-016LF	2 x 8	14.0/.55	16.4/.65	8.2/.32	2 (SHEET 1)	10087010-016LF
90311-018LF	2 x 9	16.0/.63	18.4/.72	9.2/.36	2 (SHEET 1)	10087010-018LF
90311-020LF	2 x 10	18.0/.71	20.4/.80	10.2/.40	2 (SHEET 1)	10087010-020LF
90311-022LF	2 x 11	20.0/.79	22.4/.88	11.2/.44	2 (SHEET 1)	10087010-022LF
90311-024LF	2 x 12	22.0/.87	24.4/.96	12.2/.48	2 (SHEET 1)	10087010-024LF
90311-026LF	2 x 13	24.0/.95	26.4/1.04	13.2/.52	2 (SHEET 1)	10087010-026LF
90311-028LF	2 x 14	26.0/1.02	28.4/1.12	14.2/.56	2 (SHEET 1)	10087010-028LF
90311-030LF	2 x 15	28.0/1.10	30.4/1.20	15.2/.60	2 (SHEET 1)	10087010-030LF
90311-032LF	2 x 16	30.0/1.18	32.4/1.28	16.2/.64	2 (SHEET 1)	10087010-032LF
90311-034LF	2 x 17	32.0/1.26	34.4/1.35	17.2/.68	2 (SHEET 1)	10087010-034LF
90311-036LF	2 x 18	34.0/1.34	36.4/1.43	18.2/.72	2 (SHEET 1)	10087010-036LF
90311-038LF	2 x 19	36.0/1.42	38.4/1.51	19.2/.76	2 (SHEET 1)	10087010-038LF
90311-040LF	2 x 20	38.0/1.50	40.4/1.59	20.2/.80	2 (SHEET 1)	10087010-040LF
90311-042LF	2 x 21	40.0/1.58	42.4/1.67	21.2/.83	2 (SHEET 1)	10087010-042LF
90311-044LF	2 x 22	42.0/1.65	44.4/1.75	22.2/.87	2 (SHEET 1)	10087010-044LF
90311-046LF	2 x 23	44.0/1.73	46.4/1.83	23.2/.91	2 (SHEET 1)	10087010-046LF
90311-048LF	2 x 24	46.0/1.81	48.4/1.91	24.2/.95	2 (SHEET 1)	10087010-048LF
90311-050LF	2 x 25	48.0/1.89	50.4/1.98	25.2/.99	2 (SHEET 1)	10087010-050LF

NOTES:

1. MATERIAL: UNFILLED FLAME RETARDANT NYLON, FLAME RETARDANT PER UL94V-0, COLOR: BLACK
2. SHEET 2 SHOWS THE SINGULAR LATCHING FEATURE CONFINED TO THE 2 X 2.
3. FOR USE WITH MINITEK LATCHING HEADERS WHEN MATING AND UNMATING THE FORCES WILL BE APPROX. 2.2LBS/1Kg GREATER THAN THE FORCES DETAILED IN 110-036,PAR. 3.5.3.5
4. LOGO AND CAVITY ID LOCATION ARE TO BE DETERMINED BY MANUFACTURER.
5. PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
6. THIS PRODUCT IS NOT INTENDED TO BE EXPOSED TO MANUFACTURING SOLDER PROCESSES.

mat'l. code SEE NOTE 1				surface ☒		tolerance		projection		product family MINITEK HOUSINGS	
ltr	ecr no	dr	date	tolerances unless otherwise specified		linear		MM/INCH		title	
T				angles		X*3/XX*01				MINITEK CTW HSG. DBL ROW	
				linear		XX*13/XXX*005				POLARIZATION & LATCHING	
				0*±2*		XXX*051/XXXX*0020		scale 5:1		dwg no	
				dr		D. WHITING 1991-02-15				sheet 3 of 3	
				enrg		S. OLSON 1991-02-15				size	
				chr		S. OLSON 1991-02-15				A3	
				appd		S. OLSON 1991-02-15				type	
sheet index		revision sheet								Product Customer Drawing	