

## Selector switch protective shroud



Powering Business Worldwide™

**Part no.** M22-XGWK  
**Article no.** 231274  
**Catalog No.** M22-XGWKQ

### Delivery programme

Product range			RMQ-Titan (drilling dimensions 22.5 mm)
Basic function			Accessories
Basic function accessories			Guard-ring
Single unit/Complete unit			Single unit
Function			To protect against accidental operation
Protection type			IP66
For use with			For pushbutton and selector switch actuators (button plates cannot be used)
Connection to SmartWire-DT			no

### Approvals

Product Standards	IEC/EN 60947-5; UL 508; CSA-C22.2 No. 14-05; CSA-C22.2 No. 94-91; CE marking
UL File No.	E29184
UL Category Control No.	NKCR
CSA File No.	012528
CSA Class No.	3211-03
North America Certification	UL listed, CSA certified
Degree of Protection	UL/CSA Type 3R, 4X, 12, 13

### Technical data ETIM 5.0

Low-voltage industrial components (EG000017) / Accessories for control circuit devices (EC002024)  
Electric engineering, automation, process control engineering / Low-voltage switch technology / Low-voltage switch technology (accessories) / Control circuit devices  
(accessories) (ecl@ss8-27-37-92-16 [AC0043007])

Type of electrical accessory			-
Type of mechanical accessory			Protective collar

### Dimensions

