

Name: **JONO luminaire**
1x39W T5/G5 220-240V 0/50-60Hz, 900mm
Type: 796-1845



Technical specification

Colour:	RAL9010
Material:	Base aluminium (RAL9010) / diffuser opal polycarbonate
Electronic control gear:	x
Enclosure class:	IP44
Length (mm):	900 mm
Light source:	1xT5 39W/G5
Operating frequency (Hz):	0/50-60 Hz
Rated power (W):	39W
Rated voltage (V):	220-240 V
Weight (kg):	1,350 kg
Dimensions (mm) lxxwxh:	900x55x87 mm

