



ITEM NUMBER: 5504S

CIRCUIT PROTECTION

SENTRY

ENCLOSURES IP30 ENCLOSURE

CARTON QUANTITY: 1

5504s

Metal

With mounting rail,
earth terminals and
moulded front plate

Four module

These enclosures will accommodate two or four
module Sentry RCDs or a combination of Sentry
modules, excluding contactors.

Dimensions:

5504s: 188 x 121 x 74mm
(width x height x depth)

Degree of Protection to

BS EN 60529: 1992

5504s: IP30

Precautions must be taken to maintain the IP rating.
eg. correct use of cable glands and knockouts

[Click here to view the Honeywell privacy statement](#)

Site designed & developed by viplondon



Skeleton Units

FOR MOUNTING IN A
MANTEL/CLIFTON TYPE
ENCLOSURE



6000s



6001s

6000s

ACCEPTS 14
ONE MODULE PRODUCTS
(1 INTEGRAL NEUTRAL BAR)

6001s

100A SWITCH DISCONNECTOR
AND 63A 30mA RCD.
ACCEPTS A FURTHER 10
ONE MODULE PRODUCTS
IN ANY CONFIGURATION OF
RCD PROTECTED
AND UNPROTECTED CIRCUITS
BETWEEN 2/8 AND 8/2

These units are suitable for use in
most Mantel and Clifton type
enclosures.

Factory assembled units are available
for specific installations.

DIMENSIONS:

	WIDTH	HEIGHT	DEPTH
6000s:	222 x	333 x	90mm
6001s:	222 x	333 x	90mm

Degree of Protection to
BS EN 60529: 1992 IP30

Precautions must be taken to maintain
the IP rating, eg. correct use of cable
glands and knockouts.

BS EN 60439-3: 1994

Enclosures

IP65
WEATHERPROOF
ENCLOSURE



5702s



5704s



5502s



5504s



K5592s



5604s

5702s

WEATHERPROOF
COMPLETE WITH NEUTRAL AND
EARTH TERMINAL BLOCK
ACCEPTS UP TO 4 MODULES

5704s

WEATHERPROOF
COMPLETE WITH NEUTRAL AND
EARTH TERMINAL BLOCK
ACCEPTS UP TO 8 MODULES

Typical applications for enclosures
are house extensions, garages and
small workshops.

These enclosures will accommodate
two or four module Sentry RCDs or
a combination of Sentry modules,
excluding contactors.

DIMENSIONS:

	WIDTH	HEIGHT	DEPTH
5702s:	200 x	123 x	112mm
5704s:	200 x	195 x	112mm
5502s:	149 x	76 x	76mm
5504s:	188 x	121 x	74mm
5604s:	160 x	85 x	68mm
K5592s:	185 x	119 x	66mm

Degree of Protection to

BS EN 60529: 1992

5702s: IP65

5704s: IP65

5502s: IP30

5504s: IP30

5604s: IP30

K5592s: IP30

IP30 ENCLOSURE

Switch Disconnectors Double Pole

TWO MODULE



5500s



5560s

5500s
100A 230V

5560s
63A 230V

Suitable for installation in Sentry
Consumer Units and two or four
module enclosures. Accepts direct
to busbar or cable-in / cable-out
connection. Category of duty:
AC22A for switching of resistive
and inductive loads.

Positive contact status indication in
accordance with 16th Edition IEE
Wiring Regulations
(537-02-03 and 537-03-02)

DIMENSIONS:
81 x 36 x 76mm

CABLE CAPACITY:
50mm²

BS EN 60947-3: 1992

MCBs Single Pole

TYPE B
ONE MODULE



5903s



5906s



5910s



5916s

5903s
3A 230V

5906s
6A 230V

5910s
10A 230V

5916s
16A 230V

Suitable for installation in Sentry
Consumer Units and two or four
module enclosures.

Positive contact status indication in
accordance with 16th Edition IEE
Wiring Regulations
(537-02-03 and 537-03-02)

DIMENSIONS:
83 x 18 x 74mm

CABLE CAPACITY:
3, 6, 10, 16A: 35mm²

Short-circuit breaking capacity: 6KA

BS EN 60898: 1991