



ENGLISH

Datasheet

RS Pro Stainless Steel Satin Adaptable Box



Specifications:

Part No: 471-1631

Material: 316 - 1.4404 - V4A Stainless Steel

Finish: Satin (Brushed)

Dimensions (H x W x D mm): 220 x 220 x 85

Thickness (mm): 1.2 (minimum)

Gear Plate / DIN Rail: No

Rating: IP69K, IP66 or Type 1 / 12 / 13 / 4 / 4X

DIN VDE 0470 TEIL 1/11.92

BS EN 60529 : 1992

IEC 529 : 1989

Earthing: Earth terminals & 1 earth link