

Interface module - VIP-3/PT/D25SUB/M - 2903781

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




VARIOFACE module, with push-in connections and male D-SUB miniature pin strip, for mounting on NS 35 rails, 25-pos.

The illustration shows a 37-position version



Key commercial data

Packing unit	1 pc
GTIN	 4 046356 796569
Weight per Piece (excluding packing)	157.7 g
Custom tariff number	85369010
Country of origin	United States

Technical data

Dimensions

Width	57.1 mm
Height	75.8 mm
Depth	63 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

General

Max. permissible operating voltage	125 V AC/DC
Max. perm. current (per branch)	2 A
Number of positions	25
Status display	No
Mounting position	any
Standards/regulations	IEC 60664

Interface module - VIP-3/PT/D25SUB/M - 2903781

Technical data

General

	DIN EN 50178
	IEC 62103
Rated surge voltage	1.2 kV
Pollution degree	2
Surge voltage category	II

Connection data for connection 1

Connection name	PCB connection
Connection method	Push-in connection
Conductor cross section solid min.	0.14 mm ²
Conductor cross section solid max.	2.5 mm ²
Conductor cross section stranded min.	0.14 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	26
Conductor cross section AWG/kcmil max	14
Stripping length	8 mm

Connection data for connection 2

Connection name	D-SUB connection
Number of connections	1
Connection method	D-SUB pin strip
Number of positions	25

Classifications

eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27250313
eCl@ss 5.1	27250313
eCl@ss 6.0	27242608
eCl@ss 7.0	27141152
eCl@ss 8.0	27141152

ETIM

ETIM 3.0	EC001604
ETIM 4.0	EC001604
ETIM 5.0	EC002780

UNSPSC

UNSPSC 6.01	30211824
UNSPSC 7.0901	39121421

Interface module - VIP-3/PT/D25SUB/M - 2903781

Classifications

UNSPSC

UNSPSC 11	39121421
UNSPSC 12.01	39121421
UNSPSC 13.2	39121421

Approvals

Approvals

Approvals

CSA / UL Recognized / cUL Recognized / EAC / cULus Recognized

Ex Approvals

Approvals submitted

Approval details

CSA	
mm ² /AWG/kcmil	26-14
Nominal current I _N	2 A
Nominal voltage U _N	105 V

UL Recognized	
mm ² /AWG/kcmil	26-14
Nominal current I _N	2 A
Nominal voltage U _N	125 V


cUL Recognized	
mm ² /AWG/kcmil	26-14
Nominal current I _N	2 A

Interface module - VIP-3/PT/D25SUB/M - 2903781

Approvals

Nominal voltage UN	125 V
--------------------	-------

EAC

cULus Recognized  US

Accessories

Accessories

Printing system

Printer - BLUEMARK X1 - 5147777



Printers with UV technology for printing plastic labels in UniCard format.

System cable

Cable - CABLE-D25SUB/B/S/ 50/KONFEK/S - 2302120



Round shielded cable set, with 25-pos. D-SUB female and male connectors, cable length: 0.5 m

Cable - CABLE-D25SUB/B/S/100/KONFEK/S - 2302133



Round shielded cable set, with 25-pos. D-SUB female and male connectors, cable length: 1 m

Cable - CABLE-D25SUB/B/S/150/KONFEK/S - 2302146



Round shielded cable set, with 25-pos. D-SUB female and male connectors, cable length: 1.5 m

Interface module - VIP-3/PT/D25SUB/M - 2903781

Accessories

Cable - CABLE-D25SUB/B/S/200/KONFEK/S - 2302159



Round shielded cable set, with 25-pos. D-SUB female and male connectors, cable length: 2 m

Cable - CABLE-D25SUB/B/S/300/KONFEK/S - 2302162



Round shielded cable set, with 25-pos. D-SUB female and male connectors, cable length: 3 m

Cable - CABLE-D25SUB/B/S/400/KONFEK/S - 2302175



Round shielded cable set, with 25-pos. D-SUB female and male connectors, cable length: 4 m

Cable - CABLE-D25SUB/B/S/600/KONFEK/S - 2302188



Round shielded cable set, with 25-pos. D-SUB female and male connectors, cable length: 6 m

Cable - CABLE D-SUB-S/.../.../... - 2302340



Shielded round cable, assembled with one D-SUB male and one female connector, variable cable length

Interface module - VIP-3/PT/D25SUB/M - 2903781

Accessories

Cable - CABLE-D25SUB/B/B/100/KONFEK/S - 2305473



Assembled, shielded circular cable, with D-SUB socket strip, 25-pos. from both sides, cable length: 1 m

Cable - CABLE-D25SUB/B/B/200/KONFEK/S - 2305486



Assembled, shielded circular cable, with D-SUB socket strip, 25-pos. from both sides, cable length: 2m

Cable - CABLE-D25SUB/B/B/300/KONFEK/S - 2305499



Assembled, shielded circular cable, with D-SUB socket strip, 25-pos. from both sides, cable length: 3 m

Cable - CABLE D-SUB-B-B-S/.../.../... - 2302421



Shielded round cable, assembled with two D-SUB female connectors, variable cable length

Terminal marking

Marker for terminal blocks - UC-TM 4 - 0818111



Marker for terminal blocks, Sheet, white, unlabeled, can be labeled with: BLUEMARK CLED, BLUEMARK LED, Plotter, Mounting type: Snap into tall marker groove, for terminal block width: 4.2 mm, Lettering field: 3.6 x 10.5 mm

Interface module - VIP-3/PT/D25SUB/M - 2903781

Accessories

Marker for terminal blocks - UC-TM 6 - 0818085



Marker for terminal blocks, Sheet, white, unlabeled, can be labeled with: BLUEMARK CLED, BLUEMARK LED, Plotter, Mounting type: Snap into tall marker groove, for terminal block width: 6.2 mm, Lettering field: 5.6 x 10.5 mm

Zack marker strip - ZB 5,08:UNBEDRUCKT - 0809793



Zack marker strip, Strip, white, unlabeled, can be labeled with: Plotter, Mounting type: Snap into tall marker groove, for terminal block width: 5.08 mm, Lettering field: 4.98 x 10.5 mm

Zack marker strip - ZB 22:UNBEDRUCKT - 0811862



Zack marker strip, Strip, white, unlabeled, can be labeled with: Plotter, Mounting type: Snap into tall marker groove, for terminal block width: 22 mm, Lettering field: 10.5 x 21.8 mm

Drawings

Circuit diagram

