


NO	DESCRIPTION	DATE
①	ADD 19 REF. BACKGROUND FORMAT UPDATED	03.07.11'
②	1.5 MAX. (L=250 MM)	07.04.12'



1.0 ELECTRICAL

- 1.1 FREQUENCY RANGE: DC-3 GHz
 1.2 NOMINAL IMPEDANCE: 50 OHM
 1.3 WORKING VOLTAGE: 335 VOLTS MAX.
 1.4 PROOF VOLTAGE: 750 VOLTS
 1.5 VSWR: 1.5 MAX. (L=250 MM) ①

2.0 MATERIALS

- 2.1 BODIES: BRASS PER JIS-C3604
 2.2 CENTER CONTACT: BRASS PER JIS-C3604
 2.3 INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710
 2.4 CRIMP FERRULE: BRASS PER JIS-C2700

3.0 FINISHES AND OTHERS

- 3.1 SEE BELOW TABLE FOR DETAILS.

4.0 MECHANICAL

- 4.1 INTERFACE IN ACCORDANCE WITH: MIL-STD-348A
 4.2 CABLE RETENTION 15 lbs MIN.

5.0 ENVIRONMENTAL

- 5.1 OPERATING TEMPERATURE RANGE: -55° C TO +105° C

3	HEAT SHRINK TUBE	2	BLACK
2	CABLE	1	RG-316U
1	19-03-3 174U(50Ω)	2	T.G.G
NO	DESCRIPTION	Q'TY	FINISH



APPROVED

by _____ DATE: _____

DESCRIPTION		SMA PLUG CRIMP ST.+SMA PLUG CRIMP ST.+RG-316U		品名		YH46-26	DATE	版次	REV.
製圖	DRAWN	TOLERANCE	品名	YH46-26	DATE	版次	REV.		
	Yoko	.X ±0.2	TITLE	\ROHS COMPLIANT	日期	12.03.03'	次	A-2	
檢圖	CHECK	.XX ±0.1	單位	mm(in)	DWG.NO.	99-0315			
	Arc	.XXX ±0.05	比例	SCALE					
認定	APPROVAL	ANGLE ±5°	比例	4:1					
	Angela								