

EURONORD ALN 233318



Sample photo

Order symbol:	ALN 233318
Product nbr:	7811390
Description:	Enclosure
Remarks:	Aluminium

EAN: 6418074016201
El. number:
Finland:
:

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

Dimensions:	Length	Width	Height
mm:	330	230	180
inch:	13.0	9.1	7.1

Materials:

Material:	Aluminium
Base colour:	RAL 7001
Cover colour:	RAL 7001
Cover screws material:	Stainless steel
Gasket material:	Polyurethane

Temperatures:

Short term:	-50 ... 140 °C
Continuous:	-50 ... 80 °C
Short term:	-60 ... 284 °F
Continuous:	-60 ... 175 °F

Accessories:

AM 2333	Mounting plate
ARH 2333	DIN-35 Mounting rail
MRS 28541	Wall fastening lug (2 pcs)
PH A & AH A/B	Hinge set

Rating:

Ingress Protection (EN 60529): IP 66/67/68
Impact Resistance (EN 62262): IK 08
NEMA Class: NEMA 1, 4, 4X, 12, 13

Certificates:

Underwriters Laboratories
Fimko
Gost R

