

Data Sheet

IBT 330

Battery Capacity Tester – Measurement Probe



CLIP TYPE LEAD WITH TEMPERATURE SENSOR (TES-3620-5)

From junction to probe: 70mm (black), 300mm (red, max. 1000mm) CLIP 125mm

Whole length: 1000mm