



ENGLISH

Data Sheet

RS – 1260

Humidity Temperature Meter

RS Stock No. 724-4197

FEATURE:

- Dual LCD display.
- Dew Point Reading.
- Wet bulb Reading.
- MAX/MIN with Time Stamp.
- Data Hold function.
- °C / °F Switchable.
- DATA memory and read function. (99 readings from LCD display)
- Auto Power Off.

SPECIFICATIONS

Measuring Range	Temperature : -20 to 60°C (-4 to 140°F) Humidity : 1%RH to 99%RH
Resolution	0.1°C /0.1°F /0.1%RH
Accuracy	Temperature : ±0.5°C, ±0.9°F Humidity : ±3%RH (at 25°C, 30 to 99% RH). ±5%RH (at 25°C, 1 to 30% RH).
Data Memory capacity	Manual recording : 99 data sets. (Direct reading from LCD display.)
Sampling Rate	2 times/sec
Operating Conditions	0 to 60°C (32 to 140°F) & below 99% R.H. (no condensation)
Power Source	9V Battery
Battery Life	Approx. 200 hours.
Size & Weight	193x59x26mm / 140g
Accessories	Instruction manual, Battery, Carrying case.

