



ENGLISH

Datasheet

RS Pro Twisted Steel Abrasive Cup Brush, 12500rpm

RS Stock No: **831-034**



Product Details

RS Pro twisted abrasive cup brush with steel bristle, is perfect for more aggressive cleaning jobs than standard crimped cup brushes. It is perfect for use on standard angle grinders.

Features and Benefits

- 12500 rpm maximum safe speed
- Stainless steel bristle construction
- Arbor fixing type
- 20 mm long bristle



ENGLISH

Specifications:

| | |
|--------------------|---|
| Bristle Material | Steel |
| Fixing Type | Arbour |
| Bristle Length | 20 mm |
| Face Width | 65 mm |
| Fixing Size | M10 x 1.5 |
| Maximum Safe Speed | 12500 rpm |
| Bristle Type | Twisted |
| Number of Pieces | 10 |
| Suitable For | Roughening, Deburring, Planning, Edge Honing, Structuring, Descaling/Paint Stripping & Weld Seams |