

Datasheet

RS 2 Core Unscreened Industrial Cable, PVC Sheath, 3.6mm OD, 0.22 mm² CSA 1 A, 440 V, 25m

Stock Number - 660-4027



Description:

Rated Temperature (oC): -20 ~ 80

Rated Voltage (V): 440

Flammability Test: IEC60332-1

Standard: Manufacture to Def. Stan 61.12

Part 4 & 5



ENGLISH

Construction:

Conductor: Tinned Copper

Conductor Dia. (mm): $0.20 \pm 0.008 \times 7$

Insulation: PVC

Insulation Dia. (mm): $1.2 \pm 0.05 \times 2C$

Tape: Mylar Spiral

Coverage: $\geq 115\%$

A rip cord : 210 D

Jacket: FR-PVC

Outer Dia. (mm): 3.4 ± 0.1

Colour:

The colour of the insulation: Red, Blue

The Jacket colour: Black

Marking (3times/m):

RS 6604027 7 - 2 - 2A

Performance:**Electrical Characteristics:****Max. Conductor DC Resistance****at 20°C (Ω /Km) : <92****Min. Insulation DC Resistance****at 20°C ($M\Omega \cdot KM$) : >200****Current Rating: 1 A**