



Sample photo

Order symbol: ALN 061005
Product nbr: 7811080
Description: Enclosure
Remarks: Aluminium

EAN: 6418074016041
El. number:
Finland:
:

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		100	66	46	Ingress Protection (EN 60529): IP 66/67/68
inch:		3.9	2.6	1.8	Impact Resistance (EN 62262): IK 08
Materials:					NEMA Class: NEMA 1, 4, 4X, 12, 13
Material:		Aluminium			Certificates:
Base colour:		RAL 7001			
Cover colour:		RAL 7001			
Cover screws material:		Stainless steel			
Gasket material:		Polyurethane			
Temperatures:					
Short term:		-50 ... 140 °C			
Continuous:		-50 ... 80 °C			
Short term:		-60 ... 285 °F			
Continuous:		-60 ... 175 °F			
Accessories:					
ARM 0610		DIN-15 Mounting rail			
MR 75003		Selftapping taptite screw M3			
MRS 28540		Wall fastening lug (2 pcs)			

