

Welded sleeve VEGABAR 66/67, VEGAWELL 52

For process fitting

- GA** Thread G1½ (DIN 3852-A) / 316L
- Outer dimensions**
- T** 65x39.5mm
- Q** 69x19mm
- Seal**
- X** without
- Material**
- V** 316L
- Certificate / Standard**
- B** C 3.1-Certificate/Mat.
- X** without

ESMBR66.

Straining clamp

Suitable for VEGABAR series 60 and VEGAWELL



- Material**
- 27363** Stainless steel 316L

2.

Closing screw VEGAWELL 52, VEGABAR 66/67



Version / Material

- GA** Screw connection G1½ (DIN 3852-A) PN3 / 316L
- GB** Screw connection 1½NPT (ASME B1.20.1) PN3 / 316L

WLVSCHR.