

Specification Grade 20 AMP Duplex GFCI Receptacle, White

2095W



features & benefits

The most durable GFCI available with patented SafeLock™ Protection that ensures that if critical components are damaged and ground fault protection is lost, power to the receptacle is disconnected. Prevents line-load reversal miswire with no power to the face or downstream receptacles if wired incorrectly for added safety. Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.

- **High-impact-resistant, thermoplastic construction** for superior strength and durability.
- **Captive screws** make for easier installation.
- **Extra-long strap for better sheet rock contact** eliminates "floaters" yet takes standard wall plate.
- **Back wire clamp** allows for fast installation of ground wires.
- **Trip indicator light (LED)** makes it easy to identify trip conditions.
- Side or internal screw-pressure-plate back wire with #10-#14 AWG solid or stranded copper wire.
- **Two back wire holes per terminal.**
- **Ground screw has a back wire clamp for easy installation.**
- **10kA short circuit rating.**
- **Mounting screws are shipped captive in the device and wall plate for easier installation.**
- **Extra-long strap.**
- **Button colors match the device face.**
- **Dual-direction test and reset buttons.**
- **Class A rated GFCI.**
- **Supplied with matching TP26 nylon wall plate.**
- **Tri-drive screws.**
- **10kA short circuit rating.**
- For covering patents, see www.legrand.us/patents.

specifications

General Info

Color: White

Available Colors: Ivory, White, Brown, Gray, Black, Red, Light Almond

Type: Specification Grade

Style: Decorator

Assembly/Installation Information

Mounting Hardware Included: Yes

Listing Agencies/Third Party Information

RoH S: No

CSA Standard: C22.2 No. 42, 144

CUL Listing No: E42190

cULus: Yes

cUL Standard: Yes

Federal Spec: Yes

Fed Spec Number: WC596

UL Listing No: UL498

UL Listed: Yes

UL Standard: Yes

UN SPS C: 39121614

Dimensions

Depth U S: 0.98"

Height U S: 4.2"

Length U S: 4.20"

Width U S: 1.72"

Technical Information

Amps: 20A

NEMA Configuration Number: 5-15R

NEMA Rating: WD-1, WD-6

Volts: 125V

Volts A C: 125

Grade Type: Specification

Buy American Act Compliance

Country of Origin: CHINA

Buy American Act Status: No