



Save as PDF



Peli lights - 1900 Flashlights for industry



Unlike other torches in the market that have a yellowish beam, the MityLite 1900 uses a hi-intensity Xenon lamp that produces a powerful, bright beam. Use this compact torch to cut through thick smoke, fog, and dust. It is submersible and comes with a twist on/off lens shroud. The 1900 is ideal for any situation. Powered by 2 AAA alkaline cells.



Peli lights - 1900 Flashlights for industry

ANSI FL1 Specifications

LIGHT SOURCE.	High	
	Xenon	
BATTERIES	2 AAA Alkaline (Included)	
CHARGE TIME	N/A	
VOLTAGE	3	
LENGTH	10.4 cm (4.09")	
WEIGHT W/ BATTERIES	0.09 kg (3 oz.)	
WEIGHT W/O BATTERIES	0.02 kg (0.75 oz.)	

LIGHT OUTPUT RUNTIME (hours/min) BEAM DISTANCE (meters) PEAK BEAM INTENSITY (candela) WATER RESISTANT	FL1 STANDARD	High	
		1h 30m	
		45m	
		571cd	

Materials

Body	Lens	Shroud	Switch Type
Xenon Polymer Resin	Polycarbonate Resin	Xenon Polymer Resin	Twist On/Off Lens Shroud
Clip	Contact, Spring & Retainer	O-Ring	Night Vision Film
N/A	Phosphore/Bronze	Ethylene Propylene	N/A

Configuration

Cat. #	Description

Peli lights - 1900 Flashlights for industry Accessories

Cat. #	Description

Approvals

- Class I, Div. 2; Gp ABCD, T3C; Class II; Div. 2; Gp G.

- Ex ib e IIC T4 IP67 IEC Ex TSA 06.0021X

- Class I, Div. 1, GP C,D, T3C CONFORMS TO STD UL 783