

Reflector

BLOWN REFL 63MM 40W 240V P

0015550

Range features



PRODUCT OVERVIEW

Ordering number	15550
Light colour	825 Homelight
Technology	Incandescent
Lamp shape	Reflector
Lamp finish	Aluminium
Dimmable	yes
Cap/Base	E27
Type	Standard Reflector
Beam angle(°)	35
Colour temperature (K)	2500
Watt (Nominal) (W)	40
Voltage (V)	240

Reflector

BLOWN REFL 63MM 40W 240V P

0015550

DATA TABLE

General data

Ordering number	15550
Technology	Incandescent
Average life (Nominal) (h)	1000
Lamp shape	Reflector
Lamp finish	Aluminium
Dimmable	yes
Cap/Base	E27
Type	Standard Reflector
Product name	BLOWN REFL 63MM 40W 240V P
Starting time (max) (s)	instant full light
Fixture rating	Open
IEC Reference	IEC 60064
IEC Reference 2	IEC 60432
Intended purpose	General lighting
Special purpose lamp	No
Transformer required	No

Optical data

Light colour	825 Homelight
Beam angle(°)	35
Colour temperature (K)	2500
Peak intensity (cd)	325

Electrical data

Watt (Rated) (W)	40
Watt (Nominal) (W)	40
Voltage (V)	240
Current (A)	0.167

Physical data

Lamp Length (mm) - C/L	104.5
Max. Lamp Diameter (mm) - D	63

Reflector

BLOWN REFL 63MM 40W 240V P

0015550

TECHNICAL DRAWINGS

