

△ 接点部までの嵌合長さ。
MATING LENGTH TO CONTACT POINT.


- TERMINAL : PHOS-BRO.(t=0.32)

CONTACT AREA	: GOLD PLATED	0.1MICROMETER MIN.
TAIL AREA	: TIN PLATED	1.0MICROMETER MIN.
OVER PLATED	: NICKEL PLATED	1.0MICROMETER MIN.

メッキ : 錫メッキ 1マイクロメートル以上
下地メッキ : ニッケル 1マイクロメートル以上

△3 パターンはくり止め用金具
FITTING NAIL FOR PREVENTION OF FOOT PRINT PEELING.

16



- △ テール及び金具の平坦度は、0.15 以下とする。
COPLANARITY OUT OF SPECIFICATION.
TAIL : 0.15 MAX.
NAIL : 0.15 MAX.

- | | | | | |
|------|------|----|----------------------|---------|
| 34.7 | 31.2 | 29 | 52207-3067 | 30 |
| 33.7 | 30.2 | 28 | 52207-2967 | 29 |
| 32.7 | 29.2 | 27 | 52207-2867 | 28 |
| 31.7 | 28.2 | 26 | 52207-2767 | 27 |
| 30.7 | 27.2 | 25 | 52207-2667 | 26 |
| 29.7 | 26.2 | 24 | 52207-2567 | 25 |
| 28.7 | 25.2 | 23 | 52207-2467 | 24 |
| 27.7 | 24.2 | 22 | 52207-2367 | 23 |
| 26.7 | 23.2 | 21 | 52207-2267 | 22 |
| 25.7 | 22.2 | 20 | 52207-2167 | 21 |
| 24.7 | 21.2 | 19 | 52207-2067 | 20 |
| 23.7 | 20.2 | 18 | 52207-1967 | 19 |
| 22.7 | 19.2 | 17 | 52207-1867 | 18 |
| 21.7 | 18.2 | 16 | 52207-1767 | 17 |
| 20.7 | 17.2 | 15 | 52207-1667 | 16 |
| 19.7 | 16.2 | 14 | 52207-1567 | 15 |
| 18.7 | 15.2 | 13 | 52207-1467 | 14 |
| 17.7 | 14.2 | 12 | 52207-1367 | 13 |
| 16.7 | 13.2 | 11 | 52207-1267 | 12 |
| 15.7 | 12.2 | 10 | 52207-1167 | 11 |
| 14.7 | 11.2 | 9 | 52207-1067 | 10 |
| 13.7 | 10.2 | 8 | 52207-0967 | 9 |
| 12.7 | 9.2 | 7 | 52207-0867 | 8 |
| 11.7 | 8.2 | 6 | 52207-0767 | 7 |
| 10.7 | 7.2 | 5 | 52207-0667 | 6 |
| 9.7 | 6.2 | 4 | 52207-0567 | 5 |
| 8.7 | 5.2 | 3 | 52207-0467 | 4 |
| 7.7 | 4.2 | 2 | 52207-0367 | 3 |
| C | B | A | MATERIAL NO. | 極數 |
| | | | MODEL NO. 52207-**67 | CIRCUIT |

MATERIAL NO.		極数
MODEL NO.	52207-**67	CIRCUIT




注記

1. 製品番号 52207-**67 の梱包状態はアクチュエータがロックした状態とする。
詳細寸法については図面 SD-52207-064 を参照下さい。
IN THE PACKAGE, ACTUATOR OF PART NO.52207-**67 SHOULD BE LOCKED
RE DETAILED DIMENSIONS, SEE SD-52207-064


2. 梱包数量: 1000個/リール
NUMBER OF CONNECTORS: 1000PCS/REEL

3. リードテープ長さ(LEAD TAPE LENGTH)

トップテープ TOP TAPE トップテープ TOP TAPE
リーダー部 LEADER PART 未接着部 NON-BONDED PART



4. トップテープの剥離強度: 0.1~1.3N (10gf~130gf) (剥離方向は下図参照)
尚、本規格値は、出荷時に適用。(但し、輸送時に剥離が発生しない事。)
PEELING OFF FORCE OF TOP TAPE: 0.1~1.3N (10gf~130gf)
(PEELING DIRECTION AS SHOWN IN FOLLOWING FIG.)
THIS REQUIREMENT SHOULD BE APPLIED AT SHIPMENT.(PEEL OFF SHOULD NOT BE ALLOWED, DURING TRANSPORTATION.)



5. 材料 (MATERIAL)

キャリアテープ (CARRIER TAPE): ポリプロピレン (POLYPROPYLENE)

トップテープ (TOPTAPE): PET, PE, PEF

リール (REEL): ポリスチレン (PS) <リサイクル材を含む>



POLYSTYRENE(PS) <RECYCLE MATERIAL CONTAINED>

6. 本製品は 52207-**85 の金メッキ品である。

THIS PRODUCT IS GOLD PLATING OF 52207-**85.

7. 本製品は乾燥剤入り、ハイバリア梱包仕様である。


THIS PRODUCT IS HIGH BARRIER PACKAGE WITH DESICCANT.



DETAIL "F"

MODEL No.52207-**60

REVISED EC NO.: J2009-2061 G DRAWN:TKON CHKD:HMATSUMOTO APPR:NUKITA	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	
		10 UNDER	± 0.2	DRAWN BY M.UMEDA	DATE 2005/03/03	TITLE 1.0 FPC CONN. ZIF SMT WITH EMBSTP PKG -LEAD FREE-			
		10 OVER 30 UNDER	± 0.25	CHECKED BY K.TOYODA	DATE 2005/03/03				
		30 OVER	± 0.3	APPROVED BY N.UKITA	DATE 2005/03/03		 MOLEX INCORPORATED		
		ANGULAR ±1 °		MATERIAL NO.		DOCUMENT NO.			SHEET NO.
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE SHEET 2		SD-52207-065			1 OF 5
		REV	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						




24	29.4	25.4	18.5	15	11.7	17.3	52207-1160	11
			17.5	14	10.7	16.3	52207-1060	10
			16.5	13	9.7	15.3	52207-0960	9
			15.5	12	8.7	14.3	52207-0860	8
			14.5	11	7.7	13.3	52207-0760	7
			13.5	10	6.7	12.3	52207-0660	6
			12.5	9	5.7	11.3	52207-0560	5
			11.5	8	4.7	10.3	52207-0460	4
16	21.4	17.4	10.5	7	3.7	9.3	52207-0360	3
キャリアテープ幅 CARRIER TAPE WIDTH	H	E	(D)	(C)	(B)	(A)	MATERIAL NO. MODEL NO. 52207-**60	極数 CKT.

REVISED EC NO.: J2009-2061 2009/05/20 DRWN:TKN CHKD:HMATSUMOTO 2009/05/21 APPR:NUKITA 2009/05/21 G	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
		10 UNDER	±0.2	DRAWN BY M.UMEDA	DATE 2005/03/03	TITLE 1.0 FPC CONN. ZIF SMT WITH EMBSTP PKG -LEAD FREE-				
		10 OVER 30 UNDER	±0.25	CHECKED BY K.TOYODA	DATE 2005/03/03					
		30 OVER	±0.3	APPROVED BY N.UKITA	DATE 2005/03/03	MOLEX INCORPORATED				
		ANGULAR ±1 °		MATERIAL NO.		DOCUMENT NO.		SHEET NO.		
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SD-52207-065		2 OF 5			
REV		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								

SEE TABLE

SD-52207-065

2 OF 5



SECT:W-W

32mm 幅 キャリアテープ
32mm WIDTH CARRIER TAPE

32	37.4	33.4	4.0	0.5	23.5	20	16.7	22.35	52207-1660	16
			4.2	0.6	22.5	19	15.7	21.35	52207-1560	15
			4.2	0.6	21.5	18	14.7	20.35	52207-1460	14
			4.2	0.6	20.5	17	13.7	19.35	52207-1360	13
			4.2	0.6	19.5	16	12.7	18.35	52207-1260	12
キャリアテープ幅 CARRIER TAPE WIDTH	H	E	(G)	(F)	(D)	(C)	(B)	(A)	MATERIAL NO.	極数 CKT
									MODEL NO. 52207-***60	

REVISED EC NO.: J2009-2061 DRAWN: T KON CHKD: H MATSUMOTO APPR: N UKITA	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
		10 UNDER	± 0.2	DRAWN BY M. UMEDA	DATE 2005/03/03	TITLE 1.0 FPC CONN ZIF SMT WITH EMBSTP PKG -LEAD FREE-				
		10 OVER 30 UNDER	± 0.25	CHECKED BY K. TOYODA	DATE 2005/03/03					
		30 OVER	± 0.3	APPROVED BY N. UKITA	DATE 2005/03/03	MOLEX INCORPORATED				
		ANGULAR ±1 °		MATERIAL NO.		DOCUMENT NO.				SHEET NO.
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SD-52207-065				3 OF 5
REV		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								

F


E

D

C

B

A



SECT:Z-Z

44mm 幅 キャリアテープ
44mm WIDTH CARRIER TAPE

44	49.4	45.4	—	—	34.5	30	27.7	33.35	52207-2760	27
			—	—	33.5	30	26.7	32.35	52207-2660	26
			—	—	32.5	29	25.7	31.35	52207-2560	25
			—	—	31.5	28	24.7	30.35	52207-2460	24
			—	—	29.5	26	22.7	28.35	52207-2260	22
			—	—	28.5	25	21.7	27.35	52207-2160	21
			—	—	27.5	24	20.7	26.35	52207-2060	20
			—	—	26.5	23	19.7	25.35	52207-1960	19
			—	—	25.5	22	18.7	24.35	52207-1860	18
キャリアテープ幅 CARRIER TAPE WIDTH	H	E	(G)	(F)	(D)	(C)	(B)	(A)	MATERIAL NO.	極数 CKT.
									MODEL NO.	

REVISED EC NO: J2009-2061 DRWN:TKN CHKD:HMATSUMOTO APPR:NUKITA G	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
		10 UNDER	±0.2	DRAWN BY M.UMEDA	DATE 2005/03/03	TITLE 1.0 FPC CONN ZIF SMT WITH EMBSTP PKG -LEAD FREE-				
		10 OVER 30 UNDER	±0.25	CHECKED BY K.TOYODA	DATE 2005/03/03					
		30 OVER	±0.3	APPROVED BY N.UKITA	DATE 2005/03/03	MOLEX INCORPORATED				
		ANGULAR ±1 °		MATERIAL NO.						
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SD-52207-065		4 OF 5		
	REV			SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					

