

## Crimping pliers - CRIMPFOX-RCT 16-1 - 1212731

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Crimping pliers, for uninsulated tube lugs, 10 - 16 mm<sup>2</sup>, indent and HEX crimp

### Why buy this product

- Ergonomically designed handles ensure an optimum grip and help avoid fatigue when working.
- Crimping pliers for uninsulated tube lugs
- Compact and lightweight design
- Unlockable pressure lock



### Key commercial data

Packing unit	1 pc
GTIN	 4 046356 857901
Weight per Piece (excluding packing)	701.6 g
Custom tariff number	82032000
Country of origin	Sweden

### Technical data

#### Dimensions

Length (b)	304 mm
Height	70 mm
Width (a)	30 mm

#### General

Color	black
Compression	Indent crimp
Type of contact	CU conduit lugs
Designation	Crimping position 1
Min. cross section	4 mm <sup>2</sup>
Max. cross section	6 mm <sup>2</sup>

## Crimping pliers - CRIMPFOX-RCT 16-1 - 1212731

### Technical data

#### General

AWG min	12
AWG max	10
Designation	Crimping position 2
Max. cross section	10 mm <sup>2</sup>
AWG max	8
Designation	Crimping position 3
Max. cross section	16 mm <sup>2</sup>
AWG max	6

### Classifications

#### eCl@ss

eCl@ss 4.0	21040301
eCl@ss 4.1	21040301
eCl@ss 5.0	21040301
eCl@ss 5.1	21040301
eCl@ss 6.0	21043811
eCl@ss 7.0	21043811

#### ETIM

ETIM 3.0	EC001186
ETIM 4.0	EC000168
ETIM 5.0	EC000168

#### UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518