

Cable protection end sleeve - WP-SC PA HF 42,5 BK - 3240987

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




End sleeves as cable protection

Image shows WP-TS PA HF 10.0 BK version



Key commercial data

Packing unit	25 pc
Minimum order quantity	25 pc
GTIN	 4 046356 711050
Weight per Piece (excluding packing)	6.34 g
Custom tariff number	39174000
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Length (b)	25 mm
Inner diameter (f)	33.80 mm
Outside diameter	42.50 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 115 °C
---------------------------------	-------------------

General

Color	black
Components	Halogen-free
Inflammability class according to UL 94	V0
Material	PA

Cable protection end sleeve - WP-SC PA HF 42,5 BK - 3240987

Classifications

eCl@ss

eCl@ss 4.0	27141131
eCl@ss 4.1	27141131
eCl@ss 5.0	27141131
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120

ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC002584
ETIM 5.0	EC002584

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411

Approvals

Approvals

Approvals

UL Recognized / LR

Ex Approvals

Approvals submitted

Approval details

UL Recognized

LR
