

# LED LENSER® P2BM

A slim and powerful mini LED torch which fits palm, pocket or key-ring. This makes it an ideal starter or extra torch for anyone who needs bright white light, yet may not be able or does not wish to carry a heavier-bodied torch. The P2BM only weighs 36g and measures just 102mm in length – about two-thirds the length of a pen. From just one economical AAA battery it emits 16 lumens visible light, beaming it up to 25 metres into the distance. Using Blue Moon Focus technology, it emits pure white light surrounded by a distinctive and rather beautiful blue circle. This light can be easily focused for a wider flood or telescopic spot beam with an easy-slide Speed Focus on the head of the torch. With a robust housing cast in aircraft-grade aluminium the P2BM is a dependable torch for everyday and rugged use. Supplied with battery, belt pouch, key-ring and pocket clip

As a leading international brand of hand-held torches and head lamps, LED Lenser is renowned for superior German engineering, outstanding performance, and state-of-the-art technologies, such as the patented Advanced Focus System and Smart Light Technology. Constantly driving innovation to provide class-leading lighting instruments, LED Lenser is the brand of choice for professional tradesmen, emergency services personnel, search & rescue teams and serious outdoor enthusiasts. LED Lenser hand torches and head lamps deliver breath-taking, bright homogenous white light, that turns night into day and simply has to be seen to be believed. Using only the finest materials, such as energy-efficient CREE LED light chips, aircraft-grade aluminium and gold-plated contacts, they are renowned for quality and have a reputation for reliability that is second to none.

- Slim-line torch with handy key-ring attachment
- Energy efficient LED light-chip
- State-of-the-art, reliable German engineering
- Blue Moon Focus System™ delivers a brighter, whiter beam of light
- Robust, yet lightweight aircraft-grade aluminium housing
- Speed Focus™ enables smooth single-handed beam focusing
- Pocket clip – simple, safe attachment
- Superior rear tail cap switch
- Water and dust resistant. IPX54

## Technical Information

Size: 102 x 15.5mm Ø

Power: 16 lumens

Run Time: up to 7 hours

Beam Distance: up to 25m

Weight: 36 grams

Supplied with : Key-ring, pocket clip, belt/storage pouch and Duracell® battery (1xAAA)

Code	Colour	Packaging	Barcode
8402	Black	Gift Box	4029113840200