

LOC	DIST	REV	DATE	APP
6	14			



ZONE	CD	DESCRIPTION	DATE	APP
E		REVISED PER 0720-0220-93	4/19/94	gdp

METRIC

DIMENSIONS LISTED IN mm [INCHES]

WIRE RANGE	E13288 Listed
6 AWG SOLID OR STRANDED	6 AWG STRANDED
6 AWG SOLID OR STRANDED	NOT APPLICABLE

△ STAMP AMP SIZE APPROX AS SHOWN



AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER
1-800-522-6752

FOR APPLICATION
TOOLING INFORMATION

TOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY
1-800-526-5142

MAX RECOMMENDED OPERATING
TEMPERATURE:
170°C MAX

VOLTAGE RATING:
NOT APPLICABLE

WIRE CROSS SECTIONAL AREA RANGE:
10.5-16.8mm² [20,800-33,100] CIR MILS
SOLID OR STRANDED

DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS ARE IN MILLIMETERS
TOLERANCES:
FRACTIONS DECIMALS
± .1 ± .1
± .05 ± .05

FINISH
TIN PLATE
0.00254 [0.00100] MIN
TIN PER MIL-1-10727

DR 3-24-93
TA-SHOWMAN
DATE 3-24-93
DRAWN BY

APPROVED BY
DATE 3-24-93
JL MCKLEY

APPLICATION SPEC
WEIGHT

500	LOOSE PIECE, BOX	36808-1
-	LOOSE PIECE	36808
QTY	PACKAGE TYPE	PART NO

AMP AMP Incorporated
Harrisburg, PA 17105-3608

TERMINAL, RING TONGUE,
SOLISTRAND™

SIZE CASE CODE DRAWING NO
G 00779 C-36808

SCALE 4:1 SHEET 1 OF 1

CUSTOMER DRAWING