






















Locking bayonnet on housing

Style	Ordering number	Cable entry			Description	Outline drawing dimensions in mm
Surface-mounted housing bottom entry						
		PG	PG	PG		
	41.51.32.00				HA.32.AGD	
	51.41.51.32.00				HA-K.32.AGD	
With cover! side entry standard construction						Panel cut-out 
	41.61.32.07	21			HA.32.SGD.1.21	
	41.61.32.80		21		HA.32.SGD.1.21.Z	
	41.61.32.08	2x21			HA.32.SGD.2.21	
	41.61.32.96		2x21		HA.32.SGD.2.21.Z	
	51.41.61.32.07	21			HA-K.32.SGD.1.21	
	51.41.61.32.80		21		HA-K.32.SGD.1.21.Z	
	51.41.61.32.08	2x21			HA-K.32.SGD.2.21	
	51.41.61.32.96		2x21		HA-K.32.SGD.2.21.Z	
high construction						
	49.61.50.07	21			HD.50.SGD.1.21	
	49.61.50.80		21		HD.50.SGD.1.21.Z	
	49.61.50.08	2x21			HD.50.SGD.2.21	
	49.61.50.96		2x21		HD.50.SGD.2.21.Z	
	49.61.50.09	29			HD.50.SGD.1.29	
	49.61.50.81		29		HD.50.SGD.1.29.Z	
	49.61.50.48	2x29			HD.50.SGD.2.29	
	49.61.50.97		2x29		HD.50.SGD.2.29.Z	
	51.49.61.50.07	21			HD-K.50.SGD.1.21	
	51.49.61.50.80		21		HD-K.50.SGD.1.21.Z	
	51.49.61.50.08	2x21			HD-K.50.SGD.2.21	
	51.49.61.50.96		2x21		HD-K.50.SGD.2.21.Z	
	51.49.61.50.09	29			HD-K.50.SGD.1.29	
	51.49.61.50.81		29		HD-K.50.SGD.1.29.Z	
	51.49.61.50.48	2x29			HD-K.50.SGD.2.29	
	51.49.61.50.97		2x29		HD-K.50.SGD.2.29.Z	