

SURGE SUPPRESSOR, RC COUPLING, AC 48...127V,
DC 70...150V, F. CONT. RELAYS A. MOTOR CONT.
SZ S00,



General technical data:		
product brand name		SIRIUS
Product designation		surge suppressor
Size of contactor		S00
Design of the surge suppressor		with RC elements
Ambient temperature		
• during storage	°C	-40 ... +80
• during operation	°C	-25 ... +60

Control circuit/ Control:		
Type of voltage of the control supply voltage		AC/DC
Control supply voltage frequency		
• 1 rated value	Hz	50
• 2 rated value	Hz	60
Control supply voltage 1		
• at DC		
— Initial rated value	V	70
— Final rated value	V	150
• at AC		

- at 50 Hz Initial rated value
- at 50 Hz Final rated value
- at 60 Hz Final rated value
- at 60 Hz Initial rated value

V	48
V	127
V	127
V	48

Installation/ mounting/ dimensions:

Mounting position		any
Mounting type		clip-on
Width	mm	28
Height	mm	46
Depth	mm	9

Certificates/ approvals:

Certificate of suitability CE / UL / CSA / CCC

General Product Approval	Declaration of Conformity	Test Certificates	Shipping Approval
			
	UL	EG-Konf.	ABS

[spezielle
Prüfbescheinigunge
n](#)

[Typprüfbescheinigu
ng/Werkszeugnis](#)

Shipping Approval



Shipping Approval	other	Railway
	Umweltbestätigung	Bestätigungen
	Bestätigungen	Schwingen/Schocke n
		
	VDE	

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RT29161CC00>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RT29161CC00>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RT29161CC00&lang=en



last modified:

07.12.2015