

5925UJI065L51-10 DOM23 ALU

EAN 4031582311099

Swivel castor with wheel brake, housing made of Polyamide, with blind hole for furniture fittings.
Wheel centre made of Polyamide, Tread: TENTEprene (thermoplastic rubber). Plain bearing

Technical Data

Wheel diameter	65 mm
Width of Tread	7 mm
Castor width	42 mm
Centre hole	10 mm
Dome-Ø	23 mm
Swivel Interference	154 mm
Overall height	68 mm
Temperature	- 10 / + 40 °C
Standard	EN 12528
Weight	0.101 kg
Swivel Radius	77 mm
Hardness of tread	A 87 Shore
Load capacity	50 kg
Load capacity (static)	100 kg



Roll performance	+	+	+	+	+
Movement noise	+	+	+	+	+
Attrition	+	+	+	+	+
Corrosion resistance	+	+	+	+	+

5925UJI065L51-10 DOM23 ALU

EAN 4031582311099

