

APPROVAL CERTIFICATE NO. E6558

(DAT 94001324)

As to Test Reports Nos.: 02R0868, CCA BSA 136, 02A9700650

it is stated that the following product:

REWIRABLE CONNECTORS

Type designation	2P+E S.S. C15
Rated voltage	250V
Rated current	10A
Type of application	for hot conditions
Type of terminals	MV = screw terminals
Material of the cover	thermoplastic
Cable exit	axial
Series	-

(Follows Description of the Products)

of the Firm: *BULGIN COMPONENTS PLC (1993 / 411)*
BYPASS ROAD BARKING ESSEX IG11 OAZ (GB)
manufactured in the factory of:
(95002381) ESSEX IG11 OAZ (GB)

is in conformity with:

CEI 23-13 - II Ed. 1987 (EN 60320-1 - 1988)

Variante V1 1990 (Amdt. 1 - 1989)

CEI EN 60320-1 A11 - 1995 + CEI EN 60320-1 EC 1995

therefore according to essential requirements of the L.V.D. 73/23 and 93/68 EEC

and is authorized to the use of the mark: *IMQ*

Hayward L.
IMQ

This Approval Certificate may be revoked according to what specified in the Rules under the clauses concerning the renouncement or the revocation of the use of the IMQ Marks.

*** This is a translation from the Italian text, which prevails in case of doubts ***

Date of issue 15/06/90

Up-dating 02/12/97

Supersedes 15/06/90 which is to be intended withdrawn

Copy of this Approval Certificate

shall be kept in the place of production.

IMQ models: 1

This Approval Certificate includes 1 annex

