




NO	DESCRIPTION	DATE
①	H8 REF. → 8.0 HEX. $\phi 3.7^{+0.15}_{-0.05}$ → $\phi 3.7$ REF. DEL (Ø2.1) (2) (Ø6.5) DEL PIN CHUCK 0.3X4X4 GROOVE BACKGROUND FORMAT UPDATED ADD STRIPPING DIMENSION	03.03.09'
②	ADD 2 STAMPING DEL CABLE RETENTION	06.04.10'
③	ADD VOLTAGE RATING DEL SOLDER/	05.06.13'
④	335 → 500	11.27.13'



1.0 ELECTRICAL

1.1 FREQUENCY RANGE: DC-1.8 GHz

1.2 NOMINAL IMPEDANCE: 50 OHM

1.3 VOLTAGE RATING: 500 VOLTS MAX. ③ ④

2.0 MATERIALS

2.1 BODIES: BRASS PER JIS-C3804

2.2 CENTER CONTACT: BRASS PER JIS-C3804

2.3 CRIMP FERRULE: BRASS PER JIS-C2700

3.0 FINISHES AND OTHERS

3.1 SEE BELOW TABLE FOR DETAILS.

4.0 MECHANICAL


4.1 FOR USE WITH RG174U OR SIMILAR STYLE CABLE

4.2 CABLE ATTACHMENT: OUTER: CRIMP, INNER: CRIMP/SOLDER


4.3 CRIMP SIZE REQUIRED: CONTACT: 1.8 (0.71) HEX. CRIMP TOOL ③
 FERRULE: 3.9 (1.54) HEX. CRIMP TOOL
 4.8 (1.81) HEX. CRIMP TOOL

5.0 ENVIRONMENTAL

5.1 OPERATING TEMPERATURE RANGE: -40° C TO +60° C



① STRIPPING DIMENSION
 SCALE 2:1



APPROVED

by _____ DATE: _____

NO	DESCRIPTION	MATERIAL	Q'TY	FINISH
5	CRIMP FERRULE	BRASS	1	NICKEL
4	CENTER CONTACT	BRASS	1	GOLD
3	NUT	BRASS	1	NICKEL 100μ" MIN.
2	INSULATION	POM	1	NONE
1	BODY	BRASS	1	NICKEL 100μ" MIN.



DESCRIPTION		FME STRAIGHT JACK CRIMP	
製圖	DRAWN	TOLERANCE	品名
檢圖	Yoko	XX ±0.2	23-02-5 D.G.N 174U
認圖	CHECK	XX ±0.1	DATE
認定	Arc	XXX ±0.05	01.08.93'
	APPROVAL	ANGLE ±5°	版次
	Angela		A-4
		單位	UNIT
		mm(in)	DWG.NO.
		SCALE	23-0010
		比例	4:1