



Datasheet

ENGLISH

規格: MICROPHONE SPECIFICATIONS

項目:

1. ITEM: DESKTOP MICROPHONE

型號:

2. PART NO.: 3603955

電氣規格:

3. ELECTRONICAL SPECIFICATIONS:

3.1 Directional Characteristics : Omni-Directional

3.2 Frequency : 70 Hz ~ 16,000 Hz

3.3 Impedance : $200\Omega \pm 30\%$ (at 1,000 Hz)

3.4 Sensitivity : $-66\text{ dB} \pm 3\text{ dB}$ (0 dB = 1 v\|u bar
1,000 Hz indicated by open circuit)

3.5 Operating Voltage : Phantom Power; 9V~48V D.C.

機械規格:

4. MECHANICAL SPECIFICATIONS:

4.1 Dimension : $\varnothing 80 \times 272\text{ mm}$

4.2 Connector : 3-Pin XLR(male)

測試規範:

5. METHOD OF MEASUREMENT:

According to JIS C-5502

測試儀器:

6. TEST INSTRUMENT :

Brüel & Kjær – Type 2012 with digital turntable system

曲線圖:

7. FREQUENCY RESPONSE CURVE:

