


## Slave protocol chip - IBS SUPI 3 QFP - 2746087

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Slave protocol chip, for INTERBUS (QFP 100)



### Key commercial data

Packing unit	66 pc
Minimum order quantity	66 pc
GTIN	 4 017918 153588
Weight per Piece (excluding packing)	8.02 g
Custom tariff number	85423290
Country of origin	Japan

### Technical data

#### Dimensions

Width	20 mm
Length	15 mm

#### Ambient conditions

Ambient temperature (storage/transport)	5 °C ... 30 °C (at max. 60 %)
---	-------------------------------

#### Module

IC power supply voltage	5 V DC $\pm$ 10 %
Typical current consumption	20 mA
Connection method	Remote bus, local bus or installation remote bus
Interface	INTERBUS
Internal data length	8 bytes internally, external expansion is possible up to 64 bytes
User interface	MFP interface, digital I/O (8 IN/8 OUT, 16 IN/16 OUT), parallel port for microprocessor

#### General

Type	QFP 100 (PLCC 84 has been discontinued!)
------	--

# Slave protocol chip - IBS SUPI 3 QFP - 2746087

## Classifications

### eCl@ss

eCl@ss 4.0	27250201
eCl@ss 4.1	27250201
eCl@ss 5.0	27250203
eCl@ss 5.1	27249201
eCl@ss 6.0	27242605
eCl@ss 7.0	27242605
eCl@ss 8.0	27242605

### ETIM

ETIM 2.0	EC001433
ETIM 3.0	EC001601
ETIM 4.0	EC001601
ETIM 5.0	EC001601

### UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201404
UNSPSC 13.2	43201404

## Approvals

### Approvals

---

Approvals

GOST

---

Ex Approvals

---

Approvals submitted

---

### Approval details

GOST
------

