

Dimensions

Part Number Height (mm) Width (mm) Depth (mm)

NHRS6SL	230	239	120
NHRS9SL	230	290	120
NHRS12SL	230	340	120
NHRS17SL	230	435	120

6 Way Flexible Split-load Unit

	MS Rating	MCB Ways		RCD Rating		
		Min	Max		Min	Max
NHRS6SL	100Amp	80Amp 30mA				
					2	4
					3	3
					4	2

9 Way Flexible Split-load Unit

	MS Rating	MCB Ways		RCD Rating		
		Min	Max		Min	Max
NHRS9SL	100Amp	80Amp 30mA				
					3	6
					4	5
					5	4
					6	3

12 Way Flexible Split-load Unit

	MS Rating	MCB Ways		RCD Rating		
		Min	Max		Min	Max
NHRS12SL	100Amp	80Amp 30mA				
					3	9
					4	8
					5	7
					6	6
					7	5
					8	4
					9	3

17 Way Flexible Split-load Unit

	MS Rating	MCB Ways		RCD Rating		
		Min	Max		Min	Max
NHRS17SL	100Amp	80Amp 30mA				
					5	12
					6	11
					7	10
					8	9
					9	8
					10	7
					11	6
					12	5