

## 947A - HIGH POWER IRONS - 230 V | 947A.400



### Description

- Power range from 50 to 400 W.
- Supplied with an angled tip.
- Very high yield with excellent robustness.
- Shape designed for difficult access.
- Shiny copper tips.
- Stainless steel heating body tube.
- These irons meet the requirements of the EN 60335 - 2 - 45 standard.
- Tips:
  - 947.50P1 diam. 6 mm.
  - 947.80P1 diam. 8 mm.
  - 947.100P1 diam. 10 mm.
  - 947.200P1 diam. 15 mm.
  - 947.300P1 diam. 20 mm.

### Information

L [mm] 320

[g] 960