

SSD42SSBS - Break Stem Open

General Part Information		
Product Description		SSD42SSBS
Article Number		22000.00
Rivet Type	i	Break Stem Open
Standard Bulk Pack Quantity		10000.00
Application / Features	i	



Geometry / Dimensions / Performance		
Head Style	i	Domed
Body Diameter Ø (mm)		3.20
Body Length (mm)		6.40
Min. Grip Range (mm)		1.60
Max. Grip Range (mm)		3.20
Min. Hole Diameter (mm)		3.30
Max. Hole Diameter (mm)		3.40
Min. Flange Diameter (mm)		6.04
Max. Flange Diameter (mm)		6.65
Flange Thickness (mm)		1.10
Mandrel Diameter (mm)		1.93
Nominal Shear Strength (N)		2400.00
Nominal Tensile Strength (N)		3000.00

Material / Finish / Weight		
Body Material	i	Stainless Steel
Mandrel Material		Stainless Steel
Finish		Clean
Weight per thousand (kg)		1.23