

Features & Benefits

- 1 High speed engine**- provides excellent efficiency with high quality results
- 2 Simple stylish variable temperature guide:** Comprehensive control for users of all experience
- 3 Release lever:** Function to solve any miss-feeding problems by releasing the document
- 4 Auto switch off after 1 hour**
- 5 Only 5 minutes 'Warm up' period**
- 6 Entrance highlighted**- by orange line helps guide the users placement of pouch into machine
- 7 Lightweight, stylish and compact** – ideal for the modern office environment

Stylish and fast! Fastest A4 laminator on the Market.–

This A4 laminator is the fastest A4 laminator on the market without compromising on lamination quality!

Expect the standard high quality laminating finish in approx 43% less time than the other laminators.

Using this machine lamination productivity can increase significantly. Complete 100 A4 pouches in one hour. Remember time is money!!

Perfect choice for the busy office environment

Protect and preserve from ID sized documents through to standard A4 items with 2x75mic (150 total) to 2x125mic (250total) pouches.

Extend the lifetime of your menus, reference documents etc. for increased rigidity of document for items such as diplomas and certificates use 2x125mic(250Total) pouches.

- **112 standard** A4 pouches per hour
- **Stylish and slim** body design which can be easily stored
- Digital contents designed for more **accurate temperature** control which delivers increased lamination consistency.
- **Lightweight** product so perfect for offices where machines are shared

Technical Specifications

Photo quality	Yes
Heat-up Time (75 mic)	5 min.
Speed mm/min.	500
Temperature control	Variable
Cold Lamination	No
Speed control	Fixed
Rollers	2
Max. Document size	A4 241 mm
Max. pouch thickness	2x125 Micron (250 Total)

Ready Light	Yes
Release Function	Yes

A4, A5, A6 & A7

-

-

Pouch counter	-
Auto switch off	Yes, after 1 hour
Time to laminate 1 Standard A4 Pouch	32 sec.

A4 Laminates / hr*	100
High Speed Pouches Laminates / hr*	No

Warranty	2 years
Dimensions	445x130x94
Certification	GS / TÜV / CE

Weight	2.2 kg
Power Consumption Watts / Amps	500W/2.2A



Product Codes:

EU 4400431

UK 4400432

