

## Crimping pliers - CRIMPFOX-CX 6,48 - 1212095

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Crimping pliers, for coaxial connectors, 5.41 mm, 6.48 mm, 1.69 mm, HEX crimp

### Why buy this product

- Lateral conductor entry
- Unlockable pressure lock



### Key commercial data

Packing unit	1 pc
GTIN	 4 046356 453882
Weight per Piece (excluding packing)	437.8 g
Custom tariff number	82032000
Country of origin	Sweden

### Technical data

#### Dimensions

Length (b)	198 mm
Height	59 mm
Width (a)	18 mm

#### General

Compression	HEX crimp
Type of contact	Coaxial connectors
Designation	Crimping position 1
	Crimping position 2
	Crimping position 3
Die station	Crimping position 4
	Crimping position 5

# Crimping pliers - CRIMPFOX-CX 6,48 - 1212095

## Classifications

### eCl@ss

eCl@ss 4.0	21040301
eCl@ss 4.1	21040301
eCl@ss 5.0	21040301
eCl@ss 5.1	21040301
eCl@ss 6.0	21043811
eCl@ss 7.0	21043811

### ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001186
ETIM 5.0	EC000168

### UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518

## Approvals

### Approvals

---

Approvals

EAC

---

Ex Approvals

---

Approvals submitted

---

### Approval details

EAC
-----

## Accessories

Accessories

Die

## Crimping pliers - CRIMPFOX-CX 6,48 - 1212095

### Accessories

Replacement die - CRIMPFOX-CX 6,48/DIE - 1212286



Spare die for CRIMPFOX-CX 6,48

---

### Mounting material

Replacement spring - CRIMPFOX/ SPR-3 - 1212036



Spare recuperating spring

---

### Drawings

Pictogram



Product drawing

