





NO	DESCRIPTION	DATE
①	MODIFICATION PARTS ⑤ DEL CABLE RETENTION	05.21.10'
②	DEL CONTACT SOLDER	11.24.11'
③	WORKING VOLTAGE → VOLTAGE RATING DEL PROOF VOLTAGE	06.17.13'



STRIPPING DIMENSION
SCALE 4:1

1.0 ELECTRICAL

- 1.1 FREQUENCY RANGE: DC-6 GHz
1.2 NOMINAL IMPEDANCE: 50 OHMS
1.3 VOLTAGE RATING: 170 VOLTS MAX. ③
1.4 VSWR: 1.35 MAX.

2.0 MATERIALS

- 2.1 BODIES: BRASS PER JIS-C3604
BERYLLIUM COPPER PER ASTM B196 UNS C17300
2.2 CENTER CONTACT: BRASS PER JIS-C3604
2.3 INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710
2.4 CRIMP FERRULE: BRASS PER JIS-C2700

3.0 FINISHES AND OTHERS

- 3.1 SEE BELOW TABLE FOR DETAILS.

4.0 MECHANICAL

- 4.1 INTERFACE IN ACCORDANCE WITH: BS EN 122340
4.2 FOR USE WITH RG178U OR SIMILAR STYLE CABLE
4.3 CABLE ATTACHMENT: OUTER: CRIMP, INNER: SOLDER
4.4 CRIMP SIZE REQUIRED: FERRULE: 2.8(.110) HEX. CRIMP TOOL

5.0 ENVIRONMENTAL

- 5.1 OPERATING TEMPERATURE RANGE: -55° C TO +155° C

6	CAP	BRASS	1	GOLD 3 μ" MIN.
5	BODY	BRASS	1	GOLD 3 μ" MIN.
4	CENTER CONTACT	BRASS	1	GOLD 30 μ" MIN.
3	INSULATION	TEFLON	1	NONE
2	WASHER	BERYLLIUM COPPER	1	GOLD 3 μ" MIN.
1	CRIMP FERRULE	BRASS	1	GOLD
NO	DESCRIPTION	MATERIAL	Q'TY	FINISH



APPROVED

by _____ DATE: _____

DESCRIPTION			MMCX RIGHT ANGLE PLUG									
製圖	DRAWN	TOLERANCE		品名	37-02-5		T.G.G	178U	日期	DATE	版次	REV.
	Yoko	X	±0.2	TITLE	\ROHS COMPLIANT		<500>	07.24.00'		B-3		
檢圖	CHECK	XX	±0.1	單位	UNIT	DWG.NO.	37-0009					
	Angela				mm(in)							
認定	APPROVAL	XXX	±0.05	比例	SCALE							
	Angela				ANGLE ±5°							