

## Ferrule - AI 1,5 - 8 RD-B - 3201592

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Ferrule, Sleeve length: 8 mm, Length: 14 mm, Color: red




The illustration shows version AI 1,5 - 8 in red

### Why buy this product

- The taped ferrules were developed specifically for the crimping machine CF 3000 -2,5
- Available in the main color ranges up to 2.5 mm<sup>2</sup>
- Can be used to wire all modular terminal blocks, especially those of the CLIPLINE complete system



### Key commercial data

Packing unit	1000 pc
Minimum order quantity	1000 pc
GTIN	 4 017918 126223
Weight per Piece (excluding packing)	0.16 g
Custom tariff number	85369010
Country of origin	Germany

### Technical data

#### Dimensions

Length (b)	14 mm
Sleeve length	8 mm
Inner dimension of the insulating collar (d)	3.4 mm
Ferrule diameter	1.8 mm
Insulating collar thickness	0.3 mm
Sleeve wall thickness	0.15 mm

#### Ambient conditions

Short-term temperature	120 °C
Max. permanent temperature	105 °C

# Ferrule - AI 1,5 - 8 RD-B - 3201592

## Technical data

### General

Color	red
Components	free from silicone and halogen
Inflammability class according to UL 94	HB
Material	E-CU

## Classifications

### eCl@ss

eCl@ss 4.0	27060701
eCl@ss 4.1	27060701
eCl@ss 5.0	27400201
eCl@ss 5.1	27400201
eCl@ss 6.0	27400201
eCl@ss 7.0	27400201
eCl@ss 8.0	27400201

### ETIM

ETIM 2.0	EC000005
ETIM 3.0	EC000005
ETIM 4.0	EC000005
ETIM 5.0	EC000005

### UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	27121703
UNSPSC 11	27121703
UNSPSC 12.01	27121703
UNSPSC 13.2	27121703

## Approvals

### Approvals

---

#### Approvals

CSA / CSAus / cCSAus

---

#### Ex Approvals

---

Approvals submitted

# Ferrule - Al 1,5 - 8 RD-B - 3201592

## Approvals

### Approval details

CSA 

CSAus

cCSAus

## Drawings

Dimensioned drawing

