

Revolution- or Stroke Counters

Types 101/103
301/309



- 4- or 5 digit display
- Without reset
- With or without case
- Miniature size

CASE


Counters in this series are available with surface-mounting case, with flush-mounting case or without any housing.

TECHNICAL DATA

Display	4 or 5-digit, depending on version
Digit height	4.2 mm
Mounting	depending on version
Case	plastic (POM) black
Weight	approx. 5 g, with case approx. 9 g
Counting mode	Revolution counter: + (-) adding in the specified direction, subtracting in reverse direction. Stroke Counter: + is fixed, adding
Transmission ratio	1:1 or 1:10, depending on version
Max. speed	Revolution counter: 1.000 rpm, at a transmission ratio of 1:10 max. 100 rpm. Stroke counter: max. 500 strokes/min., switching distance min. 46°, max. 49°
Torque	Revolution counter: 0.05 Ncm, Stroke counter: 1.0 Ncm
Reset	none

DIMENSIONS


Type 101/301
surface-mounting case



Types 101/103 301/309

DIMENSIONS
Typ 103/309 flush mounting case

Technical data



ORDER INFORMATION Revolution Counters

Ratio

1:1

1:10

Case	Number of digits	Actuation/sense of rotation			
		Bz	Bw	Bz	Bw
Surface	4	0 101 605	0 101 606*	0 101 607	0 101 608
	5	0 101 609	0 101 610	–	–
	flush	4	0 103 605	0 103 606	0 103 607
		5	–	–	–
flush	4	0 101 505	0 101 506	0 101 507	0 101 508
	5	0 101 613	0 101 614*	0 101 615*	0 101 616
	flush	4	0 103 505	0 103 506	0 103 507
		5	–	–	–

Stroke Counter

Case	Number of digits	Actuation/sense of rotation			
		Bz	Bw	Bz	Bw
Surface	4	0 301 505	0 301 506	0 301 507	0 301 508
	5	0 301 509	0 301 510	0 301 511	0 301 512
flush	4	0 309 505*	0 309 506*	0 309 507*	0 309 508*
	5	0 309 509	0 309 510*	0 309 511*	0 309 512*
without	4	0 301 401*	0 309 402	–	–
	5	0 301 405*	–	0 301 407*	0 301 408*

Stroke lever 0 600 007
For further stroke levers see accessories

* on request
Inquire for other versions