


DO NOT SCALE
DIMENSIONS IN mm

METRIC



THIRD ANGLE
PROJECTION

NOTES:


- 1 TO DETERMINE DIMENSIONS TAKE N=NR. OF POS.
FOR EXAMPLE, 10 POS., $N \times 2,54 = 25,4$ mm.
FOR ORDER NR. USE BASIC NR. + NR. OF POS.
FOR EXAMPLE, 2x 2 POS. = 216604-2 (SHORTEST VERSION)
2x65 POS. = 6-216604-5 (LONGEST VERSION)
- 2 HOUSING MATERIAL, GREEN GLASSFILLED POLYESTER, UL 94V-0
CONTACT MATERIAL, PHOSPHORBRONZE.
- 3 PLATING, UNDERCOATING, 1,3 μ m Ni
AT CONT. PLACE, 0,8 μ m Au
AT SOLDER-TINES, 3,0-5,0 μ m Sn
- 4 MATES WITH 0,63 SQUARE/ROUND MODU POSTS.
- 5 CONTACT-POINT.
- 6 RECOMMENDED P.C. BOARD-THICKNESS, 1,6 mm.
- 7 PRINTED: BASIC PARTNUMBER, THE WORD "AMP", PRODUCTION DATE
AND A DASHED LINE OVER THE LENGTH OF HOUSING TO
INDICATE CONTACT MATING SIDE.




SECTION B-B/TOP VIEW



SECTION A-A




REAR VIEW



BOTTOM VIEW

RECOMMENDED P.C. BOARD-HOLE LAYOUT



				FINISH		MATERIAL		PARTNUMBER	
-	-	-	-	-	-	CUSTOMER DRAWING		FOR REFERENCE ONLY	
-	-	-	-	-	-	© COPYRIGHT 1991 BY AMP HOLLAND B.V.		WILL NOT BE UPDATED	
H1	EU00-0011-03	TISZA KISS	ZITZ	20 MAY 03	ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN AND/OR PATENTS PENDING.				
H	EH-0467-97	JvL	RB	06-05-97	THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION DEC, 1991				
G	EH-1294-96	RDB	RDB	07 NOV 96			AMP HOLLAND B.V. 's-Hertogenbosch, The Netherlands.		
F	H-8257	LvdH	WRA	17 APR '92	NAME HV 190 HOR. ASS'Y DUAL ROW				
E	ECN H9408	WRA	WRA	19-12-91	GOLD VERSION				
LTR.	REVISION RECORD	DR.	CHK.	DATE	(MAX. 2X65 POSITIONS)				
DR.	W.R. ANNOKKEE	CHK.	R. de Bliock	APP.	R. SHEETS	DWG. No.	REV. LTR.	SHEET	
DATE:	19-12-91	DATE:	07 NOV 95	DATE:	07-NOV-95	C-216604	H1	1 OF 1	A2