

Product Information



IDG100x35-Ø8

EAN 4031582347203

Wheel centre made of Aluminium, Tread: heat resisting silicone rubber, damping, self-lubricating bushing

Technical Data	
Wheel diameter	100 mm
Width of Tread	35 mm
Axle Hole-Ø	8 mm
Hub length	45 mm
Temperature	- 30 / + 250 °C
Standard	EN 12533
Weight	0.354 kg
Hardness of tread	A 75 Shore
Load capacity	80 kg
Load capacity (static)	160 kg



Roll performance	+	+	+	+	+
Movement noise	+	+	+	+	+
Attrition	+	+	+	+	+
Corrosion resistance	+	+	+	+	+

