

ToLEDo Retro Candle

ToLEDo RT Candle ST 400LM E27 SL

0027289

Range features



PRODUCT OVERVIEW

Ordering number	0027289
Technology	LED
Light colour	Homelight
Energy class	A++
Average life (Rated) (h)	10000
Lamp shape	Candle
Lamp finish	Satin
Dimmable	No
Cap/Base	E27
Type	ToLEDo Retro Candle
EAN code	5410288272894
CRI (Ra)	80
Colour temperature (K)	2700
Luminous flux (Rated) (lm)	400
Efficacy (Rated) (lm/w)	100
Watt (Nominal) (W)	4
Equivalent watt (W)	35
Voltage (V)	230-240

ToLEDo Retro Candle

ToLEDo RT Candle ST 400LM E27 SL

0027289

DATA TABLE

General data

Dry applications use only	Yes
Technology	LED
Ordering number	0027289
Energy saving lamp	Yes
Energy class	A++
Average life (Rated) (h)	10000
Average life (Nominal) (h)	10000
Lamp finish	Satin
Lamp shape	Candle
Dimmable	No
Cap/Base	E27
Type	ToLEDo Retro Candle
EAN code	5410288272894
Product name	ToLEDo RT Candle ST 400LM E27 SL
Lamp mercury content (mg)	0
Starting time (max) (s)	0.05
Warm-up time to 60% of full light (max) (s)	< 1s => 60%
Control gear required	No
Control gear availability	No
General application	Hospitality; Residential & Consumer
Intended purpose	No
No. of switching cycles before premature failure (min)	>5000
Special purpose lamp	No
Transformer required	No
Optimal operating condition (°C)	25

Optical data

Light colour	Homelight
CRI (Ra)	80
Suitable for accent lighting	No
Colour temperature (K)	2700
Luminous flux (Rated) (lm)	400
Luminous flux (Nominal) (lm)	400
Lumen maintenance at end of nominal life (%)	80
Chromaticity coordinate Y	-1
Chromaticity coordinate X	-1
Adjustable chromaticity	No

ToLEDo Retro Candle

ToLEDo RT Candle ST 400LM E27 SL

0027289

Electrical data

kWh per 1000 hours burning time	4
Efficacy (Rated) (lm/w)	100
Watt (Nominal) (W)	4
Watt (Rated) (W)	4
Equivalent watt (W)	35
Voltage (V)	230-240
Drive current (mA)	32
Lamp power factor	0.5

Physical data

Lamp Length (mm) - C/L	92
Max. Lamp Diameter (mm) - D	35
Lamp dimension equal to filament lamp equivalent	Yes

ENERGY LABEL

