


INTERFACE MODULES & SUPPORTS

RJ45 Interface Module

- Single RJ45 (8P8C) type socket to screw terminals
- Terminals marked 1 to 8 (+ Shield)
- Separate shield connection
- 35mm DIN rail mounting
- Option for 32mm (G) rail mounting
- Available with optional wall mounting plates
- 45° terminals for easy access
- RoHS compliant
- SVHC free (2012)

CIM/RJ45



SPECIFICATION

Rating	125V DC 500mA		
Cable entry	0.2-4m ² (30-12 AWG)		
Terminal screw	M3		
Strip length	6mm (0.24")		
Max terminal torque	0.5Nm (4lb-in)		
Dimensions:	Height	Width	Length
	45mm (1.77")	83mm (3.27")	34mm (1.02")

TYPE NO.	DESCRIPTION
CIM/RJ45	RJ45 to screw terminal interface. 35 mm din rail mounting