


DRG. No. C 40782		SWITCH 3BR/2663	
SHEET 1 OF 1 SHEET			
DRAWN MAA	DATE 9-8-91.	APPROVED	
TRACED M.G.	SCALE 2:1	DRAWING OFFICE <i>T. Bell</i>	SALES DEPT. J. H.

**SPECIFICATION**

ACTUATING FORCE :- 7.2 N (26 OZF) MAX.  
 RELEASE FORCE :- 1.7 N (6 OZF) MIN.  
 FREE POSITION :- 40.7 (1.6) MAX.  
 OPERATING POSITION :- 39.3 (1.55) ± 0.4  
 MOVEMENT DIFFERENTIAL 0.08 (0.003) MAX.  
 OVER TRAVEL 4.6 (0.18) (AVAILABLE)  
 FORCE EXERTED AT FULL OVERTRAVEL:-  
 16.7 N (600ZF)

**SPECIAL FEATURE :-**  
 3BR WITH LABEL TO CUSTOMERS REQUIREMENT.

**DIAGRAM OF CONNECTIONS**



①


BURGESS MICRO SWITCH COMPANY LTD

DUKES WAY, TEAM VALLEY  
 GATESHEAD 11, ENGLAND  
 TELEPHONE LOW FELD (0632) 871111

THIRD ANGLE PROJECTION

**INSTALLATION DRAWING**

DO NOT SCALE.



VIEW WITH COVER REMOVED.

DEGREE OF PROTECTION :- ENCLOSURE IP54  
 TERMINALS IP00

WEIGHT 50 g MAX

ISSUE No.	DATE	
2	22-8-91	

ALL DIMENSIONS SPECIFIED IN MILLIMETRES  
 TOLERANCES UNLESS STATED :-  
 NO DECIMAL PLACES ± 0.5 1 DECIMAL PLACE ± 0.25  
 2 DECIMAL PLACES ± 0.15 ANGULAR ± 1°  
 INCH OUNCE UNITS (IN BRACKETS)

SWITCH  
 3BR/2663

DRG. No.  
 C 40782

SHEET 1 OF 1 SHEET