

## Interface module - VIP-3/PT/FLK26 - 2903791

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




VARIOFACE module, with push-in connection and flat-ribbon cable connector, for mounting on NS 35 DIN rails, with pin strip plus short and long locking latches for socket strips, 26-pos.

Illustration shows the 50-pos. version



### Key commercial data

Packing unit	1 pc
GTIN	 4 046356 796651
Weight per Piece (excluding packing)	155.4 g
Custom tariff number	85369010
Country of origin	United States
Note	Made to Order (non-returnable)

### Technical data

#### Dimensions

Width	57.1 mm
Height	75.8 mm
Depth	63 mm

#### Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

#### General

Max. permissible operating voltage	60 V AC/DC
Max. perm. current (per branch)	1 A
Number of positions	26
Status display	No
Mounting position	any

# Interface module - VIP-3/PT/FLK26 - 2903791

## Technical data

### General

Standards/regulations	IEC 60664
	DIN EN 50178
	IEC 62103
Rated surge voltage	0.6 kV
Pollution degree	2
Surge voltage category	II

### Connection data for connection 1

Connection name	PCB connection
Connection method	Push-in connection
Conductor cross section solid min.	0.14 mm <sup>2</sup>
Conductor cross section solid max.	2.5 mm <sup>2</sup>
Conductor cross section stranded min.	0.14 mm <sup>2</sup>
Conductor cross section stranded max.	2.5 mm <sup>2</sup>
Conductor cross section AWG/kcmil min.	26
Conductor cross section AWG/kcmil max	14
Stripping length	8 mm

### Connection data for connection 2

Connection name	Controller level
Number of connections	1
Connection method	IDC/FLK pin strip (2.54 mm)
Number of positions	26

## Classifications

### eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27250313
eCl@ss 5.1	27250313
eCl@ss 6.0	27242608
eCl@ss 7.0	27141152
eCl@ss 8.0	27141152

### ETIM

ETIM 3.0	EC001604
ETIM 4.0	EC001604
ETIM 5.0	EC002780

### UNSPSC

UNSPSC 6.01	30211824
-------------	----------

# Interface module - VIP-3/PT/FLK26 - 2903791

## Classifications

### UNSPSC

UNSPSC 7.0901	39121421
UNSPSC 11	39121421
UNSPSC 12.01	39121421
UNSPSC 13.2	39121421

## Approvals

### Approvals

#### Approvals

CSA / UL Recognized / cUL Recognized / EAC / cULus Recognized

#### Ex Approvals

#### Approvals submitted

### Approval details

CSA	
mm <sup>2</sup> /AWG/kcmil	26-14
Nominal current I <sub>N</sub>	1 A
Nominal voltage U <sub>N</sub>	125 V

UL Recognized	
mm <sup>2</sup> /AWG/kcmil	26-14
Nominal current I <sub>N</sub>	1 A
Nominal voltage U <sub>N</sub>	125 V

cUL Recognized	
mm <sup>2</sup> /AWG/kcmil	26-14

## Interface module - VIP-3/PT/FLK26 - 2903791

### Approvals

Nominal current IN	1 A
Nominal voltage UN	125 V

EAC

cULus Recognized 

### Accessories

#### Accessories

#### Printing system

Printer - BLUEMARK X1 - 5147777



Printers with UV technology for printing plastic labels in UniCard format.

---

#### System cable

Cable - VIP-CAB-FLK26/0,14/0,5M - 2318622



Assembled round cable with two molded 26-pos. socket strips (1:1 connection). The cable has a 90° punched on connector and a 180° punched on connector, cable length: 0.5 m

---

Cable - VIP-CAB-FLK26/0,14/1,0M - 2318635



Assembled round cable with two molded 26-pos. socket strips (1:1 connection). The cable has a 90° punched on connector and a 180° punched on connector, cable length: 1 m

---

## Interface module - VIP-3/PT/FLK26 - 2903791

### Accessories

#### Cable - VIP-CAB-FLK26/0,14/1,5M - 2318648



Assembled round cable with two molded 26-pos. socket strips (1:1 connection). The cable has a 90° punched on connector and a 180° punched on connector, cable length: 1.5 m

---

#### Cable - VIP-CAB-FLK26/0,14/2,0M - 2318651



Assembled round cable with two molded 26-pos. socket strips (1:1 connection). The cable has a 90° punched on connector and a 180° punched on connector, cable length: 2 m

---

#### Cable - VIP-CAB-FLK26/0,14/3,0M - 2318664



Assembled round cable with two molded 26-pos. socket strips (1:1 connection). The cable has a 90° punched on connector and a 180° punched on connector, cable length: 3 m

---

#### Cable - VIP-CAB-FLK26/0,14/4,0M - 2318677



Assembled round cable with two molded 26-pos. socket strips (1:1 connection). The cable has a 90° punched on connector and a 180° punched on connector, cable length: 4 m

---

#### Cable - VIP-CAB-FLK26/0,14/6,0M - 2318680



Assembled round cable with two molded 26-pos. socket strips (1:1 connection). The cable has a 90° punched on connector and a 180° punched on connector, cable length: 6 m

## Interface module - VIP-3/PT/FLK26 - 2903791

### Accessories

Cable - VIP-CAB-FLK26-0,14/... - 2318693



Assembled round cable with two molded 26-pos. socket strips (1:1 connection). The cable has a 90° punched on connector and a 180° punched on connector, cable length: Variable

Cable - FLK 26/EZ-DR/ 50/KONFEK - 2299385



Round cable set, with two 26-pos. socket strips, (1:1 connection), cable length: 0.5 m

Cable - FLK 26/EZ-DR/ 100/KONFEK - 2299398



Round cable set, with two 26-pos. socket strips (1:1 connection), cable length: 1 m

Cable - FLK 26/EZ-DR/ 150/KONFEK - 2299408



Round cable set, with two 26-pos. socket strips (1:1 connection), cable length: 1.5 m

Cable - FLK 26/EZ-DR/ 200/KONFEK - 2299411



Round cable set, with two 26-pos. socket strips (1:1 connection), cable length: 2 m

## Interface module - VIP-3/PT/FLK26 - 2903791

### Accessories

Cable - FLK 26/EZ-DR/ 300/KONFEK - 2299424



Round cable set, with two 26-pos. socket strips (1:1 connection), cable length: 3 m

---

Cable - FLK 26/EZ-DR/ 400/KONFEK - 2299437



Round cable set, with two 26-pos. socket strips (1:1 connection), cable length: 4 m

---

Cable - FLK 26/EZ-DR/ 600/KONFEK - 2299440



Round cable set, with two 26-pos. socket strips (1:1 connection), cable length: 6 m

---

Cable - FLK 26/EZ-DR/ 800/KONFEK - 2299453



Round cable set, with two 26-pos. socket strips (1:1 connection), cable length: 8 m

---

Cable - FLK 26/EZ-DR/1000/KONFEK - 2299466



Round cable set, with two 26-pos. socket strips (1:1 connection), cable length: 10 m

---

## Interface module - VIP-3/PT/FLK26 - 2903791

### Accessories

Cable - FLK EZ-DR.../.../... - 2295059



Round cable, with preassembly, not shielded, variable cable length

---

### Terminal marking

Marker for terminal blocks - UC-TM 4 - 0818111



Marker for terminal blocks, Sheet, white, unlabeled, can be labeled with: BLUEMARK CLED, BLUEMARK LED, Plotter, Mounting type: Snap into tall marker groove, for terminal block width: 4.2 mm, Lettering field: 3.6 x 10.5 mm

---

Marker for terminal blocks - UC-TM 6 - 0818085



Marker for terminal blocks, Sheet, white, unlabeled, can be labeled with: BLUEMARK CLED, BLUEMARK LED, Plotter, Mounting type: Snap into tall marker groove, for terminal block width: 6.2 mm, Lettering field: 5.6 x 10.5 mm

---

Zack marker strip - ZB 5,08:UNBEDRUCKT - 0809793



Zack marker strip, Strip, white, unlabeled, can be labeled with: Plotter, Mounting type: Snap into tall marker groove, for terminal block width: 5.08 mm, Lettering field: 4.98 x 10.5 mm

---

Zack marker strip - ZB 22:UNBEDRUCKT - 0811862



Zack marker strip, Strip, white, unlabeled, can be labeled with: Plotter, Mounting type: Snap into tall marker groove, for terminal block width: 22 mm, Lettering field: 10.5 x 21.8 mm

---

### Drawings

## Interface module - VIP-3/PT/FLK26 - 2903791

Circuit diagram

