

## Interface module - VIP-3/PT/RJ45 - 2904290

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



VARIOFACE module with push-in connection and RJ45 connector



### Key commercial data

Packing unit	1 pc
GTIN	4 046356 813761
Weight per Piece (excluding packing)	89.6 g
Custom tariff number	85369010
Country of origin	United States

### Technical data

#### Dimensions

Width	26.6 mm
Height	75.8 mm
Depth	63 mm

#### Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

#### General

Max. permissible operating voltage	48 V AC/DC
Max. perm. current (per branch)	1 A
Number of positions	8
Status display	No
Mounting position	any
Standards/regulations	EN 50178

#### Connection data for connection 1

# Interface module - VIP-3/PT/RJ45 - 2904290

## Technical data

### Connection data for connection 1

Connection name	PCB connection
Connection method	Push-in connection
Conductor cross section solid min.	0.14 mm <sup>2</sup>
Conductor cross section solid max.	2.5 mm <sup>2</sup>
Conductor cross section stranded min.	0.14 mm <sup>2</sup>
Conductor cross section stranded max.	2.5 mm <sup>2</sup>
Conductor cross section AWG/kcmil min.	26
Conductor cross section AWG/kcmil max	14
Stripping length	8 mm

### Connection data for connection 2

Connection name	RJ45 connection
Number of connections	1
Connection method	RJ45 socket
Number of positions	8

## Classifications

### eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27250313
eCl@ss 5.1	27250313
eCl@ss 6.0	27242608
eCl@ss 7.0	27141152
eCl@ss 8.0	27141152

### ETIM

ETIM 3.0	EC001604
ETIM 4.0	EC001604
ETIM 5.0	EC002780

### UNSPSC

UNSPSC 6.01	30211824
UNSPSC 7.0901	39121421
UNSPSC 11	39121421
UNSPSC 12.01	39121421
UNSPSC 13.2	39121421

## Approvals

### Approvals

# Interface module - VIP-3/PT/RJ45 - 2904290

## Approvals


Approvals


CSA / UL Recognized / cUL Recognized / EAC / cULus Recognized


Ex Approvals

Approvals submitted


## Approval details

CSA 	
mm <sup>2</sup> /AWG/kcmil	26-14
Nominal current IN	1 A
Nominal voltage UN	48 V

UL Recognized 	
mm <sup>2</sup> /AWG/kcmil	26-14
Nominal current IN	1 A
Nominal voltage UN	48 V

cUL Recognized 	
mm <sup>2</sup> /AWG/kcmil	26-14
Nominal current IN	1 A
Nominal voltage UN	48 V

EAC
-----

cULus Recognized 
--

## Drawings

## Interface module - VIP-3/PT/RJ45 - 2904290

Circuit diagram

